



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Side**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Mechanical Attachment

Thread Size	PG29
Locking Device Location	Housing

Body Features

Primary Product Color	Gray
Cable Entry Location	Side

Product Type Features

Hood & Base Connector Product Type	Hood
------------------------------------	------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1319320129-000
H32A-TS-PG29



TE Part # T3609290101-000
DLX-29-MS



TE Part # T2010322101-000
HA-016-M 17-32



TE Part # T2010162101-000
HA-016-M

Also in the Series | [HDC IP65](#)



Rectangular Connector Hoods & Bases (1257)

Customers Also Bought



TE Part #CAT-D9934-A15E
Header Assembly: Wire-to-Board, 3A, Gold or Tin Plated




TE Part #CAT-D9934-A15B
Receptacle and Tab Housing: 2.5 mm Pitch, 250V



TE Part #CAT-D9934-A15
Contact: Component To Wire; 3-5A, 30-18 Wire Size




TE Part #1-917511-2
DYNAMIC D-3 REC CONT. 2L AU 0.38 L/P



TE Part #1-178138-2
DYNAMIC 3200 HDR H 3P ASSY



TE Part #1971153-1
CONN ASSY INDUSTRIAL MINI I/O



TE Part #175444-6
HYBRID I/O CAP ASSY 34P

Documents

Product Drawings

H32A-SGR-2PG29

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T1449320229-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T1449320229-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T1449320229-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English

Application Specification