



Connectors > Terminal Blocks & Strips > Modular Terminal Blocks



Modular Terminal Block Product Type: **Female Plug Terminal Block**

Primary Product Color: **Gray**

Product Spacing: **5.2 mm [.205 in]**

Number of Positions: **2**

Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**

Features

Housing Features

Housing Material	Polyamide
------------------	-----------

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-0

Electrical Characteristics

Power Loss	.4 W
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	600 V
Impulse Withstanding Voltage Rating (IEC)	8000 V
Current Rating (IEC)	24 A
Current Rating (UL)	22 A
Current Rating (CSA)	22 A
Dielectric Withstanding Voltage (Max)	2200 V
Voltage Rating (IEC)	1000 V
Voltage Rating (CSA)	600 V
Short-Time Withstanding Current Rating @ 1s	300 A

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Configuration Features

Gauge Type	A2 / 2.3 mm Dia.
------------	------------------



Number of Poles	1
Number of Positions	2

Dimensions

Main Circuit Capacity - Twin Ferrule per Spring Clamp	26 – 20 AWG
Product Depth	36.2 mm
Tool Size	3.5 mm[.138 in]
Wire Stripping Length	11 mm[.433 in]
Main Circuit Capacity - 1 Rigid Stranded Conductor per Spring Clamp	26 – 12 AWG
Main Circuit Capacity - 1 Non-Insulated Ferrule per Spring Clamp	26 – 14 AWG
Main Circuit Capacity - 1 Insulated Ferrule per Spring Clamp	26 – 14 AWG
Main Circuit Capacity - 1 Flexible Conductor per Spring Clamp	.22 – 2.5 mm²
Product Length	18.5 mm
Product Height	19.1 mm
Product Spacing	5.2 mm[.205 in]

Body Features

Product Weight	2.84 g[.11 oz]
Primary Product Color	Gray

Product Type Features

Modular Terminal Block Product Type	Female Plug Terminal Block
-------------------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC










Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1SNK900660R0000 PT-ZD	 TE Part # 1SNK149999R0000 MC512PA	 TE Part # 1SNK900609R0000 PROCAP5	 TE Part # 1SNK900637R0000 VR-ZD
 TE Part # 1SNK805214R0000 ZDK2.5-D1	 TE Part # 1SNK805213R0000 ZDK2.5-D2	 TE Part # 1SNK805015R0000 ZDK2.5-11	 TE Part # 1SNK805025R0000 ZDK2.5-11-BL
 TE Part # 1SNK805020R0000 ZDK2.5-22-BL	 TE Part # 1SNK805212R0000 ZDK2.5-D2-PE	 TE Part # 1SNK805014R0000 ZDK2.5-21	 TE Part # 1SNK805156R0000 ZD2.5-22-PE



TE Part # 1SNK140004R0000
[MC512-YL](#)



TE Part # 1SNK140000R0000
[MC512](#)



TE Part # 1SNK805150R0000
[ZDK2.5-11-PE](#)



TE Part # 1SNK805017R0000
[ZD2.5-22](#)



TE Part # 1SNK805250R0000
[ZDK2.5-D1-PE](#)



TE Part # 1SNK805223R0000
[ZDK2.5-D2-BL](#)




TE Part # 1SNK900611R0000
[UMH](#)



TE Part # 1SNK805016R0000
[ZD2.5-11](#)


Also in the Series | **ENTRELEC SNK**



[Modular Terminal Blocks\(319\)](#)



[Terminal Block & Strip Conducting Accessories\(67\)](#)




[Terminal Block & Strip Insulating Accessories\(31\)](#)

Customers Also Bought



TE Part #926984-1
[STD TIMER CONTACT](#)



TE Part #1SNK705960R0000
[EK2.5-D2](#)



TE Part #1SNK705961R0000
[EK2.5-T3](#)



TE Part #1SNK905303R0000
[JB5-3](#)



TE Part #1SNA163313R2400
[PC8-10](#)



TE Part #1SNK506150R0000
[ZS6-PE](#)



TE Part #1SNK705219R0000
[ZK2.5-D-CH2-DU-RL](#)



TE Part #1SNK705511R0000
[ZK2.5-T1](#)

1SNK805713R0000

Female Plug Terminal Block, Gray, Product Spacing 5.2 mm [.205 in], 2 Position, -55 – 110 °C [-67 – 230 °F], ENTRELEC SNK



Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1SNK805713R0000_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK805713R0000_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1SNK805713R0000_A1.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CDK2.5-E

English

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Blocks Catalogue (RUS)

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English

Essential Entrelec Terminal Blocks

French

Essential Entrelec Terminal Blocks

English

Essential Entrelec Terminal Blocks

Japanese

Agency Approvals

Bureau Veritas Marine and Offshore Certificate

English

1SNK805713R0000

Female Plug Terminal Block, Gray, Product Spacing 5.2 mm [.205 in], 2 Position, -55 – 110 °C [-67 – 230 °F], ENTRELEC SNK

