


INTERMATEABLE WITH
PATT 616
NFC C93-422 (HE308)



941 L 003 M 17-35 P A *

Series No. _____

Class _____

1 = Environmental
2 = Hi Rel

L = Lock Ring (Opt)
-- = Standard

Basic Part No. _____

Finish Symbol
(See Page 5)

Modification Code _____

Alternate Position
A, B, C, D (Omit for normal)

P = Pins, Plug side
S = Sockets, Plug side

Insert Arrangement _____

Shell Size _____

*Add Modification Code 131 for dry lubricant on inside surfaces of coupling nut.

SHELL SIZE	A MAX	B MAX
09	.573 (14.6)	.859 (21.8)
11	.701 (17.8)	.984 (25.0)
13	.851 (21.6)	1.158 (29.4)
15	.976 (24.8)	1.281 (32.5)
17	1.101 (28.0)	1.406 (35.7)
19	1.208 (30.7)	1.516 (38.5)
21	1.333 (33.9)	1.641 (41.7)
23	1.458 (37.0)	1.766 (44.9)
25	1.583 (40.2)	1.891 (48.0)

Metric dimensions (mm) are indicated in parentheses

MIL-C-38999 Series I

Glenair®

INSERT ARRANGEMENTS

SHELL SIZE REF	INSERT ARRANGEMENT DASH NO.	CONTACT SIZE: QUANTITY				ALTERNATE KEYWAY POSITIONS				
		22	20	16	12	N°	A°	B°	C°	D°
9	9-3		3							
	9-35	6								
	9-44	4					77	—	—	113
	9-98		3							
11	11-2			2						
	11-4		4							
	11-5		5							
	11-6		6							
	11-35	13					81	67	123	109
	11-98		6							
13	13-4			4						
	13-8		8							
	13-35	22					75	63	127	115
	13-98		10							
15	15-5			5						
	15-15		14	1						
	15-18		18							
	15-19		19				74	61	129	116
	15-35	37								
17	15-97		8	4						
	17-6				6					
	17-8			8						
	17-26		26				77	85	125	113
	17-35	55								
19	17-99		21	2						
	19-11			11						
	19-28		26	2						
	19-30		29	1		95				
	19-32		32				77	65	125	113
	19-35	66								
21	19-45	67								
	21-35	79								
	21-11				11					
	21-16			16						
	21-24		24							
	21-25		25				77	65	125	113
	21-27		27							
23	21-39		37	2						
	21-41		41							
	23-35	100								
	23-2	85								
	23-21			21						
	23-32		32							
	23-34		34				80	69	121	110
	23-36		36							
	23-53		53							
25	23-55		20							
	23-97			16						
	23-99			11						
	25-2	100								
	25-4		48	8						
	25-19				19					
25	25-24			12	12					
	25-29			29			80	69	121	110
	25-35	128								
	25-43		23	20						
	25-61		61							

