



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: Hood

Cable Entry Location: Top & Side

Hood & Base Locking Device Type: Locking Clip

Sealable: Yes

EU RoHS Compliance: Compliant

Features

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Mechanical Attachment

Thread Size	PG29
Hood & Base Locking Device Type	Locking Clip

Product Type Features

Hood & Base Connector Product Type	Hood
Sealable	Yes

Body Features

Cable Entry Location	Top & Side
----------------------	------------

Other



EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # T3609290101-000
DLX-29-MS



TE Part # T2040322101-000
HE-016-M 17-32



TE Part # T1410322000-000
H32B-AG



TE Part # T1710322129-000
H32B-TBF-PG29

Also in the Series | HDC IP65



Rectangular Connector Hoods & Bases
(1257)

Customers Also Bought



TE Part #T1440102120-000
H10B-SGR-M20



TE Part #T1750102132-000
H10B-TBFH-M32



TE Part #T1240100220-000
H10B-TGH-2M20



TE Part #T1340160121-000
H16B-TGH-RO-PG21



TE Part #T1510322000-000
H32B-AD-LB




TE Part #T1610482129-000
H48B-SGR-LB-PG29




TE Part #T2060122201-000
HSB-006-F 7-12



TE Part #T1330060132-000
H6B-TSH-M32



TE Part #T4112002052-000
M12,FEMALE,RA,A CODE,5P,PG9,
SILVER



TE Part #T4171210005-002
M12,FRONT MOUNTING,MALE,A,5P,
0.5M WIRE

Documents

Product Drawings
H32B-TG-PG29

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_T1220320129-000_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_T1220320129-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1220320129-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English