



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Conducting Accessories



Conducting Accessory Type: **Shield Connector**

Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**

EU RoHS Compliance: **Compliant**

EU ELV Compliance: **Compliant**

Features

Body Features

Product Weight	3.5 g[.124 oz]
----------------	----------------

Electrical Characteristics

Voltage Rating (IEC)	320 V
----------------------	-------

Dimensions

Product Width	2.84 mm[.112 in]
Product Depth	10.9 mm[.429 in]
Product Height	94 mm[3.701 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Product Type Features

Conducting Accessory Type	Shield Connector
---------------------------	------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK505060R0000
ZS4-YL



TE Part # 1SNK505062R0000
ZS4-RD




TE Part # 1SNK505321R0000
ZS4-S-T2-BL



TE Part # 1SNK505313R0000
ZS4-SP





TE Part # 1SNK506062R0000
[ZS6-RD](#)




TE Part # 1SNK505066R0000
[ZS4-BK](#)




TE Part # 1SNK505331R0000
[ZS4-S-T2-OR](#)




TE Part # 1SNK506315R0000
[ZS6-S](#)



TE Part # 1SNK506030R0000
[ZS6-OR](#)




TE Part # 1SNK505063R0000
[ZS4-PR](#)




TE Part # 1SNK506064R0000
[ZS6-BR](#)



TE Part # 1SNK505312R0000
[ZS4-S-T2.3](#)



TE Part # 1SNK505314R0000
[ZS4-SP-T2](#)




TE Part # 1SNK505330R0000
[ZS4-S-OR](#)




TE Part # 1SNK505065R0000
[ZS4-WH](#)




TE Part # 1SNK505010R0000
[ZS4](#)




TE Part # 1SNK506061R0000
[ZS6-GN](#)



TE Part # 1SNK506020R0000
[ZS6-BL](#)



TE Part # 1SNK506060R0000
[ZS6-YL](#)



TE Part # 1SNK505320R0000
[ZS4-S-BL](#)


Also in the Series | **ENTRELEC SNK**



Modular Terminal Blocks(319)



Terminal Block & Strip Conducting Accessories(67)




Terminal Block & Strip Insulating Accessories(31)

Customers Also Bought





TE Part #770988-3
MINI UMNL SOK 22-18AWG AU LP




TE Part #350705-7
UMNL SPLIT PIN 20-14 AUBR L/P




TE Part #130230
SOLIS R 12-10 6MM



TE Part #1SNK506012R0000
ZS6-4S



TE Part #1SNK506020R0000
ZS6-BL




TE Part #1SNK508311R0000
ZS10-ST-T4



TE Part #1SNK508423R0000
ZS4-D2-SF1-R1



TE Part #1SNK908303R0000
JB8-3



TE Part #1SNK910304R0000
JB10-4



TE Part #1-1879124-1

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK900600R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900600R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900600R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SHBS

English

SNK SERIES TERMINAL BLOCKS

English



[ENTRELEC Terminal Blocks Catalogue \(RUS\)](#)

[ENTRELEC Terminal Block - Master Catalog](#)

[ENTRELEC Terminal Block - Master Catalog](#)

English