




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **8**

Number of Rows: **2**

Features

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]

Packaging Features

Packaging Quantity	350
Packaging Method	Reel

Usage Conditions

Housing Temperature Rating	Standard
Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]

Termination Features

Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Method to PCB	Surface Mount

Contact Features

Contact Underplating Material	Nickel
-------------------------------	--------



Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.8 µm[31.5 µin]
Mating Square Post Dimension	.64 mm[.025 in]
PCB Contact Termination Area Plating Material Thickness	3 µm[118 µin]
Contact Shape & Form	Square
Contact Layout	Matrix
Contact Mating Area Length	5.8 mm[.228 in]
Contact Base Material	Copper Zinc, Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Pin
Contact Current Rating (Max)	5 A

Housing Features

Housing Material	PCT GF
Centerline (Pitch)	2.54 mm[.1 in]

Configuration Features

Connector Contact Load Condition	Fully Loaded
Board-to-Board Configuration	Parallel
PCB Mount Orientation	Vertical
Number of Positions	8
Number of Rows	2

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Breakaway
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Black
-----------------------	-------

Mechanical Attachment

PCB Mount Retention	Without
PCB Mount Alignment	Without



Connector Mounting Type	Board Mount
Mating Alignment	Without

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 969973-4
2x4P HV100 REC. CON, SMD, GOLD, BLISTER




TE Part # 215309-4
2X4P HV100 REC CON. TE, 8.5MM




TE Part # 925367-4
MOD 4 REC.HSG 2X04P



TE Part # 829264-4
2X 4P HV100 REC CON.B/TE, 6.2,NO KINK



TE Part # 215307-4
2X4P HV100 REC CON. TE, 7.0MM




TE Part # 216604-4
2X 4P HV190FEDERLEI

Also in the Series | AMPMODU Headers



Automotive Headers(3)




Board-to-Board Headers & Receptacles(1571)



Connector Contacts(52)




Connector Hardware(1)



PCB Headers & Receptacles(1618)




Wire-to-Board Connector Assemblies & Housings(5)



Wire-to-Board Headers & Receptacles (116)


Customers Also Bought




TE Part #87224-1
01 MODII HDR SRST UNSHRD .100



TE Part #2204534-1
ELCON MINI 3P CABLE CONN,PULL-TAB



TE Part #1123688-3
2.5 BATTERY REC ASSY 6P




TE Part #353293-6
MINI CT MT REC ASSY 6P GRAY




TE Part #5-146128-1
[03 MODII HDR SR SFMNT B/A LF](#)



TE Part #1241150-8
[8P MOD II BREAK AWAY HDR , SMD, BLISTER](#)




TE Part #4-2176237-0
[CPF A 0603 6K2 0.1% 25PPM 5K RL](#)



TE Part #178326-3
[DYNAMIC DBL ROW HDR ASSY 12P V](#)



TE Part #650131-000
[D-436-87](#)



TE Part #802442-SF
[FN2090-10-06](#)

Documents

Product Drawings

[2x4P MOD II BREAK AWAY HDR,SMD, BLISTER](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1241050-4_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1241050-4_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1241050-4_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.