

1934221-1  ACTIVE

Z-PACK | Z-PACK TinMan


TE Internal #: 1934221-1

240 Position High Speed Backplane Connector, 15 Row, 16 Column, PCB Mount Receptacle, Right Angle, Unshrouded, Z-PACK TinMan

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors



Number of Positions: 240

Row-to-Row Spacing: 1.4 mm [.055 in]

Mating Alignment: With

Mating Alignment Type: Guide Slot

Number of Rows: 15

Features

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Signal Characteristics

Data Rate	10 Gb/s
-----------	---------

Differential Impedance	100 Ω
------------------------	-------

Number of Differential Pairs per Column	5
---	---

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

UL Flammability Rating	UL 94V-0
------------------------	----------

Compatible With Approved Standards Products	UL E28476
---	-----------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Termination Post & Tail Length	2.2 mm[.087 in]
--------------------------------	-----------------

Body Features

Shield Material	Phosphor Bronze
Primary Product Color	Black

Packaging Features

Packaging Method	Tube, Box & Tube
------------------	------------------

Contact Features

PCB Contact Termination Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material Thickness	.5 µm[20 µin]
Contact Shape & Form	Dual Beam
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Type	Receptacle
Contact Current Rating (Max)	.5 A

Housing Features

Number of Shrouded Sides	0
End Wall Location	None
Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	1.9 mm[.075 in]

Product Type Features

Signal Arrangement	Differential
Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
PCB Connector Assembly Type	PCB Mount Receptacle
Shroud Style	Unshrouded

Mechanical Attachment

Guide Hardware	Without
PCB Mount Retention	With
Mating Retention	Without
PCB Mount Retention Type	Action/Compliant Tail
PCB Mount Alignment	Without
Mating Alignment	With
Mating Alignment Type	Guide Slot

Connector Mounting Type

Board Mount

Dimensions

Connector Width	31.81 mm
PCB Thickness (Recommended)	1.57 mm [.062 in]
Connector Height	24.4 mm
PCB Hole Diameter	.47 mm
Connector Length	30.55 mm
Row-to-Row Spacing	1.4 mm [.055 in]

Configuration Features

Number of Pairs	80
Number of Signal Positions	160
Backplane Architecture	Traditional Backplane
Stackable	No
Pairs per Column	5
Number of Positions	240
Number of Rows	15
Number of Columns	16
PCB Mount Orientation	Right Angle

Usage Conditions

Operating Temperature Range	-65 – 90 °C [-85 – 194 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE
2024 (241)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1934347-1
TinMan R/A Header Assy 5x16 Open



TE Part # 1934333-1
Tin Man Header Assy 5X16 left




TE Part # 1934334-1
Tin man Header Assy 5x16 Right



TE Part # 1934331-1
Tin man Header Assy 5x16 Open




TE Part # 1934332-1
Tin man Header Assy5x16 Double



TE Part # 1934348-1
TinMan R/A Header Assy 5x16 Do

Also in the Series | Z-PACK TinMan



Customers Also Bought



Documents

Product Drawings

[Tin Man Recept Assy 5 Pair 16 Column](#)

English

CAD Files

[Customer View Model](#)

[ENG_CVM_CVM_1934221-1_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model[ENG_CVM_CVM_1934221-1_B.3d_igs.zip](#)

English

Customer View Model[ENG_CVM_CVM_1934221-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[High Speed Backplane Connectors catalog - Z-PACK TinMan High Speed, High Density Backplane Connector](#)

English

[Solutions for AdvancedTCA, AdvancedTCA 300, MicroTCA, and AdvancedMC Standards Datasheet 3-1773445-8](#)

English

[Z-PACK TinMan High Speed High Density Backplane Connector Catalog 5-1773447-9](#)

English

Product Specifications[Application Specification](#)

English