



Connectors > Terminal Blocks & Strips > Modular Terminal Blocks



Modular Terminal Block Product Type: **Female Plug Terminal Block**

Block Function: **Feed-Through**

Primary Product Color: **Green & Yellow**

Product Spacing: **5.2 mm [.204 in]**

Number of Positions: **2**

Features

Housing Features

Housing Material	Polyamide 6.6
------------------	---------------

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-0

Electrical Characteristics

Impulse Withstanding Voltage Rating (IEC)	8000 V
Current Rating (IEC)	24 A
Current Rating (UL)	20 A
Short-Time Withstanding Current Rating @ 1s	300 A

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Dimensions

Product Depth	44.9 mm[1.75 in]
Tool Size	3.5 mm[.138 in]
Wire Stripping Length	11 mm[.433 in]
Main Circuit Capacity - 1 Rigid Stranded Conductor per Spring	26 – 12 AWG



Clamp		
Main Circuit Capacity - 1 Non-Insulated Ferrule per Spring Clamp		26 – 14 AWG
Main Circuit Capacity - 1 Insulated Ferrule per Spring Clamp		26 – 14 AWG
Main Circuit Capacity - 1 Flexible Conductor per Spring Clamp		.22 – 2.5 mm²
Product Width		5.2 mm[.204 in]
Product Length		44.9 mm[1.75 in]
Product Height		35.5 mm[1.38 in]
Product Spacing		5.2 mm[.204 in]
Wire Size		12 AWG

Body Features

Product Weight		5.37 g[.189 oz]
Primary Product Color		Green & Yellow

Configuration Features

Number of Levels		1
Gauge Type		A2 / 2.3 mm Dia.
Number of Poles		2
Number of Circuits		1
Block Function		Feed-Through
Number of Positions		2

Product Type Features

Modular Terminal Block Product Type		Female Plug Terminal Block
-------------------------------------	--	----------------------------

Termination Features

Termination Method to Wire & Cable		Push-in
------------------------------------	--	---------

Mechanical Attachment

Connector Mounting Type		Cable Mount (Free-Hanging)
-------------------------	--	----------------------------

Operation/Application

Circuit Application		Signal
---------------------	--	--------

Other

EU RoHS Compliance		Compliant
EU ELV Compliance		Compliant

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK900203R0000
TP2



TE Part # 1SNK905303R0000
JB5-3



TE Part # 1SNK905302R0000
JB5-2



TE Part # 1SNK140004R0000
MC512-YL



TE Part # 1SNK900201R0000
TC5-R1



TE Part # 1SNK140000R0000
MC512



TE Part # 1SNK805150R0000
ZDK2.5-11-PE




TE Part # 1SNK805017R0000
ZD2.5-22

1SNK805752R0000

Female Plug Terminal Block, Feed-Through, Green & Yellow, Product Spacing 5.2 mm [.204 in], 2 Position, Push-in, Signal, ENTRELEC SNK



TE Part # 1SNK805250R0000
ZDK2.5-D1-PE



TE Part # 1SNK805223R0000
ZDK2.5-D2-BL



TE Part # 1SNK905350R0000
JB5-50



TE Part # 1SNK900660R0000
PT-ZD




TE Part # 1SNK149999R0000
MC512PA




TE Part # 1SNK900609R0000
PROCAP5




TE Part # 1SNK900637R0000
VR-ZD




TE Part # 1SNK805214R0000
ZDK2.5-D1



TE Part # 1SNK805213R0000
ZDK2.5-D2



TE Part # 1SNK805015R0000
ZDK2.5-11




TE Part # 1SNK805025R0000
ZDK2.5-11-BL



TE Part # 1SNK900205R0000
TP4

Also in the Series | ENTRELEC SNK



Modular Terminal Blocks(319)



Terminal Block & Strip Conducting Accessories(67)




Terminal Block & Strip Insulating Accessories(31)


Customers Also Bought



TE Part #1SNK900001R0000
BAM4



TE Part #1SNA231000R0700
RC510



TE Part #1SNA233000R0100
RC610



TE Part #1SNL606010R0000
C4/6



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK805752R0000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK805752R0000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK805752R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English

Essential Entrelec Terminal Blocks

French

Essential Entrelec Terminal Blocks

English

Essential Entrelec Terminal Blocks

Japanese



Agency Approvals

Bureau Veritas Marine and Offshore Certificate

English