

9-2367346-1  ACTIVE

## DEUTSCH DT Highspeed

TE Internal #: 9-2367346-1


Single Wire Seal (SWS), VMQ, Orange, 6 mm [.236 in] Cavity

Diameter, -40 – 125 °C [-40 – 257 °F], DEUTSCH DT Highspeed

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Seals & Cavity Plugs > DT Highspeed Connector Seals and Plugs



Connector Seal & Plug Type: **Single Wire Seal (SWS)**

Primary Product Material: **VMQ**

Primary Product Color: **Orange**

Cavity Diameter: **6 mm [.236 in]**

Operating Temperature (Max): **125 °C [ 257 °F ]**

[All DT Highspeed Connector Seals and Plugs \(3\)](#)

## Features

### Housing Features

Centerline (Pitch)

4 mm [.15 in]

### Product Type Features

Connector Seal & Plug Type

Single Wire Seal (SWS)

### Body Features

Primary Product Material

VMQ

Primary Product Color

Orange

### Dimensions

Cavity Diameter

6 mm [.236 in]

### Usage Conditions

Operating Temperature (Max)

125 °C [ 257 °F ]

Operating Temperature Range

-40 – 125 °C [-40 – 257 °F]

### Other

Contains Lubricant	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) <small>Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



## Also in the Series | DEUTSCH DT Highspeed



## Customers Also Bought



## Documents

### Product Drawings

[SWS,HSD,CVTY DIA,RECTANGULAR](#)

English

---

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_9-2367346-1\\_B1.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_9-2367346-1\\_B1.3d\\_igs.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_9-2367346-1\\_B1.2d\\_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

[Application Specification](#)

English