

2213929-8

✓ ACTIVE

LUMAWISE | LUMAWISE LED Holders


TE Internal #: 2213929-8

No Driver on Board / Not Dimmable / Not Programmable, 60 VDC,  
Poke-In, Wire-to-Component, 2 Position, LUMAWISE LED Holders,  
LED Holders

[View on TE.com >](#)



Connectors > Lighting Connectors > LED Holders



Lighting Connector Features Included: Not Dimmable, Not Programmable, Not Optic Compatible, No Driver on Board, Zhaga Inspired

Operating Voltage: 60 VDC

Termination Method to Wire & Cable: Poke-In

Connector System: Wire-to-Component

Number of Positions: 2

## Features

### Housing Features

Housing Material	PBT GF
------------------	--------

### Operation/Application

Circuit Application	Power
---------------------	-------

### Contact Features

Contact Base Material	Copper Alloy
-----------------------	--------------

Contact Current Rating (Max)	3 A
------------------------------	-----

### Product Type Features

COB Substrate Thickness	1 mm
-------------------------	------

LED Holders Product Type	LED Holder
--------------------------	------------

Connector System	Wire-to-Component
------------------	-------------------

### Electrical Characteristics

Current Rating (Max)	3 A
----------------------	-----

Operating Voltage	60 VDC
-------------------	--------

### Configuration Features

Lighting Connector Features Included	Not Dimmable, Not Programmable, Not Optic Compatible, No Driver on Board, Zhaga Inspired
Number of Positions	2

### Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

### Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | LUMAWISE LED Holders



## Customers Also Bought



## Documents

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2213929-8\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2213929-8\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2213929-8\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Datasheets & Catalog Pages

### LUMAWISE LED Holder Type Z35 16\*19 flyer

English

---

## Product Specifications

### Application Specification

English

### Application Specification

English

---

## Agency Approvals

### LED Holders

English

### LED Holders CB Test Certificate to IEC 60838

English