


MULTIGIG RT 2-S

TE Internal #: 2302321-1  
56 Position High Speed Backplane Connector, 7 Row, 8 Column,  
PCB Mount Header, Right Angle, Unshrouded, 1.8 mm [.075 in]  
Centerline, MULTIGIG RT 2-S

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors



Number of Positions: 56  
Row-to-Row Spacing: 1.35 mm [.053 in ]  
Mating Alignment: With  
Mating Alignment Type: Keyed  
Number of Rows: 7

Features

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Signal Characteristics

Number of Differential Pairs per Column	2
Differential Impedance	100 Ω

Housing Features

Housing Material	LCP - GF (Liquid Crystal Polymer)
Number of Shrouded Sides	2
Centerline (Pitch)	1.8 mm[.075 in]

Product Type Features

Signal Arrangement	Differential
Connector & Contact Terminates To	Printed Circuit Board
Compatible with PCB Type	Daughtercard
Connector System	Board-to-Board
PCB Connector Assembly Type	PCB Mount Header
Shroud Style	Unshrouded

Configuration Features

Number of Pairs	16
-----------------	----



Number of Power Positions	0
Number of Ground Positions	20
Backplane Architecture	Traditional Backplane
Number of Signal Positions	4
Card Slot Centerline	20.3 mm[.8 in]
Number of Positions	56
Number of Rows	7
Number of Columns	8
PCB Mount Orientation	Right Angle
Guide Location	Unguided

Contact Features

Contact Current Rating (Max)	1 A
------------------------------	-----

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Keyed
Connector Mounting Type	Board Mount

Dimensions

Row-to-Row Spacing	1.35 mm[.053 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Not Compliant
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024 (241)  
Candidate List Declared Against: JUNE 2022 (224)  
SVHC > Threshold:  
Pb (13% in Component)

Article Safe Usage Statements:  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2000676-1  
Keyed Guide Pin, Machined, Vita 46




TE Part # 2000713-1  
RA Keyed Guide Mod, Vita 46, Machined


Also in the Series | MULTIGIG RT 2-S




Backplane Power Connectors(10)



Coax Connectors(6)




High Speed Backplane Connectors(10)




PCB RF Modules(1)

Customers Also Bought







TE Part #1-1469492-9  
MULTIGIG RT 9MM GUIDE/ESD UNKE




TE Part #5787617-8  
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,




TE Part #2015699-1  
RF CA,UMCC GEN1-GEN1,0.81MM CABLE,L100MM




TE Part #1487586-3  
USB, A-B, 28/28, WHITE, 0.16M




TE Part #2332817-1  
Vert RCPT Left End Half Multigig RT 3




TE Part #ADP-SMAF-TNCF-B  
SMA Jack to TNC Jack Bulkhead




TE Part #CONSMA007  
SMA Plug 50 Ohm Cable Crimp



TE Part #1SNG601190R0000  
EP-SG-PG9-LGR-B



TE Part #1410187-4  
MULTIGIG RT T2 7RW DC DF CT



TE Part #154763-E  
SMCB 12 M AB VV 7-03 CL \* 0007 137 E004

Documents

Product Drawings  
RA ASSY, Left Half RTM, MULTIGIG RT 2-S  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_2302321-1\_2.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_2302321-1\_2.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_2302321-1\_2.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



MULTIGIG RT 3 and RT 2-S Connectors

English

Product Specifications

Product Specification

English