

2-84953-4

✓ ACTIVE

FPC

TE Internal #: 2-84953-4

1 mm [.039 in] Centerline, Right Angle, Surface Mount, Stuffer
Actuator, Tin, 24 Position, FPC Connectors[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors



Centerline (Pitch): 1 mm [.039 in]

Mating Retention Type: **Zero Insertion Force (ZIF)**PCB Mount Orientation: **Right Angle**Contact Mating Location: **Top**Termination Method to PCB: **Surface Mount**

Features

Electrical Characteristics

Operating Voltage	200 VAC
-------------------	---------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Body Features

Primary Product Color	Natural
-----------------------	---------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Packaging Quantity	1200
--------------------	------

Operation/Application

Circuit Application	Signal
---------------------	--------

Dimensions

Connector Width	6.54 mm[.258 in]
-----------------	------------------

Accepts Flex Cable Thickness	.3 mm[.012 in]
------------------------------	----------------

Connector Height	2.56 mm[.101 in]
------------------	------------------

Connector Length	31.92 mm[1.257 in]
------------------	--------------------

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector & Contact Terminates To	Flexible Printed Circuit (FPC)
Connector Product Type	Connector Assembly
Connector System	Flex-to-Board
FPC Actuator Type	Stuffer

Contact Features

Contact Current Rating (Max)	1 A
Contact Shape & Form	Single Beam
PCB Contact Termination Area Plating Material Thickness	3.8 μ m, 2 μ m
Contact Layout	Inline
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
PCB Contact Termination Area Plating Material Finish	Bright
Contact Type	Socket
Contact Mating Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	3.8 μ m, 2 μ m
Contact Mating Location	Top
Contact Mating Area Plating Material	Tin

Configuration Features

Compatible With Wire & Cable Type	FFC, FPC
Number of Rows	1
PCB Mount Orientation	Right Angle
Number of Positions	24

Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Retention	With
PCB Mount Alignment	Without
Mating Retention Type	Zero Insertion Force (ZIF)

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	1 mm [.039 in]

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-84952-4
1MM FPC HORZ.BOTTOM CONT.
ASSY 24P

TE Part # 2-84982-4
1MM FFC SMT V ASSY 24P EMBOS

Customers Also Bought



TE Part #1-1622820-3
3520 18R 5%



TE Part #4-1462037-6
IM06JR=IM RELAY 140mW 12V



TE Part #6-1676966-1
SMW2 33R 5%



TE Part #1-2834237-2
2P REC, IP67 VERTICAL T/H CONN,
NATURE



TE Part #1241050-4
2x4P MOD II BREAK AWAY HDR,SMD,
BLISTER




TE Part #5-146128-1
03 MODII HDR SR SFMNT B/A LF



TE Part #1622603-1
LR1L 5% R47



TE Part #6-1625892-6
3W SM M/OX 5% 68K



TE Part #1-2176085-0
EP 9W (S) 330R 5%



TE Part #CD11413001
FLHTC0311-0.75-4

Documents

Product Drawings

[1MM FPC HORZ.TOP CONT.ASSY 24P](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-84953-4_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-84953-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-84953-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FPC Connector Family

English

[1-1773959-7-FPC-Connectors-CN](#)

English

Product Specifications

Product Specification

English

Agency Approvals

UL Report

English