



MICTOR

TE Internal #: 1-1658051-2
PCB Mount Header, Vertical, Board-to-Board, 56 Position, .8 mm [.031 in] Centerline, Gold Flash, Surface Mount, Power & Signal, Black, Box / Tray

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **56**
Centerline (Pitch): **.8 mm [.031 in]**

Features

Electrical Characteristics

Operating Voltage	125 VAC
Impedance	100 Ω
Insulation Resistance	2 MΩ
Dielectric Withstanding Voltage (Max)	675 VAC

Dimensions

	.186 in
Stack Height	30 mm[1.181 in]
Connector Height	29.24 mm[1.149 in]

Packaging Features

Packaging Quantity	36
Packaging Method	Tray, Box

Operation/Application

Assembly Process Feature	None
Circuit Application	Power & Signal



Mechanical Attachment

Mating Retention	With
PCB Mount Alignment Type	Locating Posts
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	Without

Termination Features

Rectangular Termination Post & Tail Width	.94 mm[.037 in]
Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Method to PCB	Surface Mount

Contact Features

	50 μin
Mating Tab Width	.38 mm[.015 in]
Contact Shape & Form	Square, Single Beam
Contact Base Material	Phosphor Bronze
Mating Tab Thickness	.2 mm[.008 in]
PCB Contact Termination Area Plating Material	Gold
Contact Mating Area Plating Material	Gold Flash
Contact Type	Pin
Contact Current Rating (Max)	1.25 A, 9.5 A

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	.8 mm[.031 in]

Configuration Features

Connector Contact Load Condition	Differential Load
Board-to-Board Configuration	Parallel
Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	56

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
-----------------------------	------------------



Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Black
-----------------------	-------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts



TE Part # 1-1658043-2
[MSB0.80RC-ASY56DP,-,F,VCTY](#)

Customers Also Bought



TE Part #CAT-104MTA-PVUMH
[PCB Header: Polyester, Vertical, 2.54 mm](#)



TE Part #3-641238-2
[02P MTA100 CONN ASSY NATL 30AU](#)




TE Part #1623401-1
[CRG0805 ZEROHM](#)



TE Part #60619-4
[CMNL SOK PTPPHBZ L/P](#)



TE Part #350423-1
[03P CMNL HDR ASSY PC NATL](#)




TE Part #282836-2
[TERMI-BLOK PCB MOUNT 90 2P.](#)



TE Part #1-2176094-7
[RP 2A 0.25W 174K 0.1% 25PPM 1K RL](#)



TE Part #8-2176093-3
[RP 2A 0.25W 75K 0.1% 25PPM 1K RL](#)



TE Part #4-1734839-0
[FPC CONN. 0.5MM PITCH T/C,40P](#)

Documents

Product Drawings

[MSB0.80PL30ASY56DP,-,F,VCTY](#)

English

CAD Files

Customer View Model



[ENG_CVM_CVM_1-1658051-2_L.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1658051-2_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1658051-2_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English