

1-1415533-1



DO NOT USE FOR NEW DESIGN

SCHRACK | SCHRACK SR6

TE Internal #: 1-1415533-1

TE Internal Description: SR6ZA040

Force Guided Relay, DIN-rail

[View on TE.com >](#)



[All Force Guided Relay, DIN-rail \(12\)](#)

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: 4,4'-isopropylidenediphenol (Bisphenol A) (.3% in component part) <small>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 2-1415042-1  
SR6ZA036

## Also in the Series | SCHRACK SR6




AC Relays(7)



DC Relays(16)



Electromechanical Relays(95)



Force Guided Relays(95)

## Customers Also Bought



TE Part #CAT-H396-CH8172  
DEUTSCH HDP20 Housings



TE Part #DTT-20-03  
CRIMP TOOL



TE Part #K1060489  
Relay 29-113-12



TE Part #K1007153  
Toggle Switch 08-1-1-13



TE Part #DRC16-70SBE-P013UK  
PLG, 70P, BLK, E, SEAL BOND, B



TE Part #K1002956  
Toggle Switch 08-4-1-13



TE Part #K1008699  
Relay 26-60-05



TE Part #SRK-PC-080-25-601  
PIN, SOLID, SIZE M8, 25mm<sup>2</sup>, AG



TE Part #2-2176245-2  
CRGS1206 5% 56R

## Documents

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1415533-1\\_B.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1415533-1\\_B.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1415533-1\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

#### Safety Relay Module SR6Z

English

---

### Product Specifications

#### Definitions General Purpose Relays

English

---

### Agency Approvals

#### CE Declaration of Conformity

English