

HD16-9-1939S-P080

✓ ACTIVE

DEUTSCH | DEUTSCH HD10, DEUTSCH HD

TE Internal #: HD16-9-1939S-P080

9 Position Housing, Housing for Female Terminals, Wire-to-Wire, Sealable, Green, Wire & Cable, Power, Cable Mount (Free-Hanging), Hybrid

[View on TE.com >](#)

Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HD10 Housings

Number of Positions: **9**Connector & Housing Type: **Housing for Female Terminals**Mating Pin Diameter: **1.6 mm [.063 in]**Connector System: **Wire-to-Wire**Sealable: **Yes**[All DEUTSCH HD10 Housings \(53\)](#)

Features

Housing Features

Housing Material	PA 66 GF15
------------------	------------

Industry Standards

IP Rating	IP6K9K, IP68
-----------	--------------

UL Flammability Rating	20mm Flame Test per Standard UL-94
------------------------	------------------------------------

Dimensions

Compatible Insulation Diameter Range	2.5 – 3.8 mm [.1 – .15 in]
--------------------------------------	----------------------------

Product Width	40.5 mm [1.59 in]
---------------	-------------------

Product Length	40.5 mm [1.59 in]
----------------	-------------------

Connector Height	41.5 mm [1.63 in]
------------------	-------------------

Packaging Features

Packaging Quantity	1
--------------------	---

Packaging Method	Package
------------------	---------

Mechanical Attachment

Strain Relief	Without
---------------	---------

Terminal Position Assurance	No
-----------------------------	----

Mating Alignment Type	Polarizing Rib
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Other

Serviceable	Yes
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Electrical Characteristics

Operating Voltage	250 VDC
Nominal Voltage Architecture	250 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Green

Contact Features

Contact Size	Size 16
Contact Type	Socket
Mating Pin Diameter	1.6 mm[.063 in]
Contact Current Rating (Max)	13 A

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	0
Connector Modification	J1939 Type II
Number of Positions	9

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) <small>Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # HD10-9BT-BK
BOOT, 9P, PLG/REC, ST, BLKTE Part # CAT-H3910-CH8172
DEUTSCH HD10 HousingsTE Part # CAT-H3910-PC1748
DEUTSCH HD10 PLUG DUST CAPSTE Part # HD10-9BT-BK-430
BOOT, 9P, PLG/REC, ST, BLKTE Part # HD10-9BT
BOOT, 9P, PLG/REC, ST, GRYTE Part # CAT-D48-SP729
DEUTSCH Sealing Plugs


Also in the Series | DEUTSCH HD




Automotive Headers(1)




Automotive Housings(53)




Connector Backshells(17)




Connector Strain Relief(5)




Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(12)




PCB Headers & Receptacles(1)




Wire-to-Board Headers & Receptacles(1)


Also in the Series | DEUTSCH HD10




Automotive Connector Caps & Covers (17)



Automotive Headers(1)




Automotive Housings(53)



Connector Backshells(17)




PCB Headers & Receptacles(1)



Wire-to-Board Headers & Receptacles (1)

Customers Also Bought

TE Part #HDP24-24-31SE-L015
REC, 31P, BLK, E, THD, 16, STE Part #M902-2041
COMP NUT, 3/6/9SZ, CBL SZ .187-.300,
HD10TE Part #HD17-9-1939S-P080
PLG, 9P, GRN, N, THREAD, J1939,
TYPE 2TE Part #2317657-1
AV25 SPM 3A MOVING RING R&G
12V FLTE Part #878129-000
207W256-3-01/42-0TE Part #5-103080-4
06 MODII HDR SRST SHRD .100CLTE Part #1-2399610-2
2POS,HVP1400,ASSY,90DEG,COD C/DTE Part #8-2399606-5
1POS,HVP1400,ASSY,180DEG,COD ETE Part #K1167031
Relay (HVR) 60-311-12-905TE Part #K1167032
Relay (HVR) 60-311-12-904

Documents

Product Drawings**PLG, 9P, GRN, N, J1939, TYPE 2**

English

CAD Files**3D PDF**

3D

Customer View Model

[ENG_CVM_CVM_HD16-9-1939S-P080_99.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_HD16-9-1939S-P080_99.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_HD16-9-1939S-P080_99.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages****DEUTSCH HD10 CONNECTOR SERIES**

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications**Application Specification**

English

Agency Approvals**UL Report**

English