



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Gang Wire Seal**
Primary Product Material: **Silicone Rubber**
Primary Product Color: **Blue**
Compatible Insulation Diameter Range: **2.45 – 3.6 mm [.097 – .142 in]**
Number of Positions: **2**

Features

Product Type Features

Connector Seal & Plug Type	Gang Wire Seal
----------------------------	----------------

Body Features

Primary Product Material	Silicone Rubber
Primary Product Color	Blue

Dimensions

Compatible Insulation Diameter Range	2.45 – 3.6 mm [.097 – .142 in]
--------------------------------------	--------------------------------

Configuration Features

Number of Positions	2
---------------------	---

Usage Conditions

Operating Temperature Range	-30 – 140 °C[-22 – 284 °F]
-----------------------------	----------------------------

Other

EU RoHS Compliance	Compliant
--------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability












Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 3-2381315-2 Power Versa-Lock PLUG, 1X2 KEY C, GWT	 TE Part # 6-2378158-2 Power Versa-Lock CAP, 1X2 KEY F	 TE Part # 9-2378159-2 Power Versa-Lock PLUG, 1X2 KEY I	 TE Part # 8-2378159-2 Power Versa-Lock PLUG, 1X2 KEY H
--	---	---	---



 TE Part # 776363-1 SEALING PLUG, SZ 16 CAVITY	 TE Part # 1-2378158-2 Power Versa-Lock CAP, 1X2 KEY A	 TE Part # 2-2378158-2 Power Versa-Lock CAP, 1X2 KEY B	 TE Part # 9-2378158-2 Power Versa-Lock CAP, 1X2 KEY I
 TE Part # 5-2378158-2 Power Versa-Lock CAP, 1X2 KEY E	 TE Part # 4-2378158-2 Power Versa-Lock CAP, 1X2 KEY D	 TE Part # 7-2378159-2 Power Versa-Lock PLUG, 1X2 KEY G	 TE Part # 3-2378158-2 Power Versa-Lock CAP, 1X2 KEY C
 TE Part # 7-2378158-2 Power Versa-Lock CAP, 1X2 KEY G	 TE Part # 3-2378159-2 Power Versa-Lock PLUG, 1X2 KEY C	 TE Part # 6-2378159-2 Power Versa-Lock PLUG, 1X2 KEY F	 TE Part # 1-2378159-3 Power Versa-Lock PLUG, 1X3 KEY A
 TE Part # 2-2378159-2 Power Versa-Lock PLUG, 1X2 KEY B	 TE Part # 1-2381315-2 Power Versa-Lock PLUG, 1X2 KEY A, GWT	 TE Part # 1-2378159-2 Power Versa-Lock PLUG, 1X2 KEY A	 TE Part # 5-2378159-2 Power Versa-Lock PLUG, 1X2 KEY E

Also in the Series | **Power Versa-Lock 5.0**

 Connector Caps & Covers(4)	 Connector Contacts(12)	 Connector Hardware(5)	 Connector Seals & Cavity Plugs(9)
---	---	--	--



Insertion & Extraction Tools(2)



Power Contacts(12)




Rectangular Power Connectors(77)

Customers Also Bought



TE Part #520963-2
ULTRA-POD 250 ASSY REC 18-14 AWG TPBR




TE Part #HD10-3-GKT
GASKET, 3SZ, BLK, HD10



TE Part #63896-1
250 FASTON REC 16-12 AWG BR



TE Part #42742-2
250 FASTON FLAG REC 18-12 AWG TPBR



TE Part #60932-2
SPLICE 2500-4700 .020 TPST




TE Part #5-2378159-2
Power Versa-Lock PLUG, 1X2 KEY E




TE Part #7-2378159-2
Power Versa-Lock PLUG, 1X2 KEY G



TE Part #776181-1
0.040 MULTILOCK RCPT



TE Part #61008-1
SPLICE 18-16 AWG .0158 TPST



TE Part #174966-2
040 MLC PLUG HSG 4P BLACK

Documents

Product Drawings
Power Versa-Lock REAR SEAL, 1X2, LargeID
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2325349-2_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2325349-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2325349-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English

Instruction Sheets

Instruction Sheet (U.S.)

English