

**1SNK900620R0000**

✓ ACTIVE

**ENTRELEC | ENTRELEC SNK**

TE Internal #: 1SNK900620R0000

Safety Cover, Used With Screw Clamp Terminal Blocks, -55 – 110 °C  
[-67 – 230 °F], ENTRELEC SNK, Terminal Block & Strip Insulating  
Accessories[View on TE.com >](#)

Connectors &gt; Terminal Blocks &amp; Strips &gt; Terminal Block &amp; Strip Accessories &gt; Terminal Block &amp; Strip Insulating Accessories

Insulating Accessory Type: **Safety Cover**Compatible With Block or Strip Type: **Screw Clamp Terminal Blocks**Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**EU RoHS Compliance: **Compliant**EU ELV Compliance: **Compliant**

## Features

### Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-2

### Body Features

Primary Product Color	Clear
Product Weight	2.6 g [.092 oz]
Primary Product Material	Polycarbonate

### Dimensions

Product Spacing	8 mm [.315 in]
Product Depth	25.05 mm [.986 in]
Product Height	49.24 mm [1.939 in]

### Usage Conditions

Installation Temperature Range	-5 – 40 °C [23 – 104 °F]
Operating Temperature Range	-55 – 110 °C [-67 – 230 °F]

### Product Type Features

Insulating Accessory Type	Safety Cover
---------------------------	--------------

### Operation/Application

Compatible With Block or Strip Type	Screw Clamp Terminal Blocks
-------------------------------------	-----------------------------

## Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: UV-329 (.5% in Component Part) <small>Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts

TE Part # 1SNK508063R0000  
ZS10-PRTE Part # 1SNK508066R0000  
ZS10-BKTE Part # 1SNK508030R0000  
ZS10-ORTE Part # 1SNK508065R0000  
ZS10-WHTE Part # 1SNK508061R0000  
ZS10-GNTE Part # 1SNK508064R0000  
ZS10-BRTE Part # 1SNK508062R0000  
ZS10-RDTE Part # 1SNK508020R0000  
ZS10-BLTE Part # 1SNK508060R0000  
ZS10-YLTE Part # 1SNK508010R0000  
ZS10


## Also in the Series | ENTRELEC SNK






Modular Terminal Blocks(319)

Terminal Block & Strip Conducting  
Accessories(67)Terminal Block & Strip Insulating  
Accessories(31)

## Customers Also Bought

TE Part #1SNK505010R0000  
ZS4TE Part #1SNK506210R0000  
ZS6-D2TE Part #1SNA206683R0400  
AJS9-BLTE Part #1SNA234000R0200  
RC810

TE Part #1SNK508020R0000  
ZS10-BLTE Part #1SNK510020R0000  
ZS16-BLTE Part #1SNK908303R0000  
JB8-3TE Part #1SNS430000Z2258  
MC812PA S1 (x100) HorizontalTE Part #1SNS430000Z2259  
MC812PA S2 (x100) HorizontalTE Part #1SNS430000Z2260  
MC812PA S3 (x100) Horizontal

## Documents

### Product Drawings

#### PL8

English

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1SNK900620R0000\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1SNK900620R0000\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1SNK900620R0000\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### PL8

English

#### SNK SERIES TERMINAL BLOCKS

English

[ENTRELEC Terminal Blocks Catalogue \(RUS\)](#)
[ENTRELEC Terminal Block - Master Catalog](#)
[ENTRELEC Terminal Block - Master Catalog](#)

1SNK900620R0000

Safety Cover, Used With Screw Clamp Terminal Blocks, -55 – 110 °C [-67 – 230 °F],  
ENTRELEC SNK, Terminal Block & Strip Insulating Accessories



English