



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Precision Resistor**

Element Type: **Thin Film**

Package Size Code: **0402**

Power Rating: **.063 W**

Resistance Value: **6.8K  $\Omega$**

Features

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	.063 W
Resistance Value	6.8K $\Omega$
Resistance Class	1k $\Omega$ – 1M $\Omega$
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.3 mm[.012 in]
Product Length	1 mm[.039 in]



Product Width	.5 mm[.02 in]
---------------	---------------

Usage Conditions

Temperature Coefficient	±25 ppm/°C
-------------------------	------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CPF-A-0402B6K8E1

Surface Mount Precision Resistor, Thin Film, 0402, .063 W, 6.8K ohm, .1 %, ±25 ppm/°C, Solder, 2 Terminations, Height .3 mm [.012 in], Neohm CPF





TE Part # 4-2176215-5  
CPF A 0402 68K 0.1% 25PPM 1K RL



TE Part # 2-2176237-5  
CPF A 0603 680R 0.1% 25PPM 5K RL



TE Part # 4-2176217-9  
CPF A 0805 10K 0.1% 25PPM 1K RL



TE Part # 6-2176216-5  
CPF A 0603 200K 0.1% 25PPM 1K RL



TE Part # 5-2176217-6  
CPF A 0805 25K 0.1% 25PPM 1K RL

Also in the Series | [Neohm CPF](#)




Surface Mount Resistors(5842)

Customers Also Bought



TE Part #2-1879208-7  
CPF 0402 120R 0.1% 25PPM 1K RL




TE Part #1217167-1  
250 FASTON,PCB TAB,TCBR



TE Part #5-1879208-0  
CPF 0402 1K1 0.1% 25PPM 1K RL



TE Part #1-1879417-2  
CPF 0603 510K 0.1% 25PPM 1K RL



TE Part #7-2176404-5  
3550 2R2 5%




TE Part #8-1676480-5  
CRG0402 1% 6K8



TE Part #2177372-3  
8POS,TAB 0.5X0.4,HEADER ASSY, CODA



TE Part #953363-1  
6pos MQS .63 header 180deg



Documents

Product Drawings

CPF A 0402 6K8 0.1% 25PPM 1K RL

English

Datasheets & Catalog Pages

Automotive Grade Thin Film Chip Resistor - Type CPF-A Series

English