



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.03 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

	.057 in
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Dimensions

Product Length	19.2 mm[.755 in]
Compatible Insulation Diameter Range	1.4 – 2.3 mm[.055 – .09 in]



Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.51 – 1.03 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1-1579007-4
EXTRACTION TOOL



TE Part # 4-1579007-3
EXTRACTION TOOL KIT



TE Part # 7-2150193-7
OCEAN_2.0_SPARE_PART_KIT-080F110OV




TE Part # 626094-1
TERMINAL, .250 FASTIN-ON REC




TE Part # 626094-2
FF .250 REC 0.5 /1.0 MM2 0.32X19.3 TPBR



TE Part # 160871-6
FF 250 REC TERMINAL FLAG 20-17 TPBR



TE Part # 626328-2
FF 250 RECEPTACLE 4.0-6.0 MM2 TPBR



TE Part # 2150193-1
OCEAN_2.0_Applicator-E-080F110OV-REM



TE Part # 2150193-2
OCEAN_2.0_Applicator-E-080F110OV-REA



TE Part # 63467-1
FF 250 REC 14-10AWG TPBR

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(207)



Insertion & Extraction Tools(2)



PCB Terminals(2)



Quick Disconnects(250)

Customers Also Bought




TE Part #776538-1
AS16,CAP ASSY,ST,08P,E SEAL,CODE A



TE Part #2-1879073-3
THS10 15R 5%



TE Part #180384-2
FF 250 REC 4-6MM2 PTBR LP



TE Part #925176-5
FF 312 3P HOUSING REC POLYAMID 6.6 BLACK




TE Part #160655-2
FASTON 110 REC 20-15 AWG PTPB




TE Part #1622243-2
LR0204 1% 47R




TE Part #7-180984-5
250 FASTON BOOT FLAG REC. 1P BLACK



TE Part #170209-1
MINI SPRING REC



TE Part #964275-2
MT2 A REC 1.6 Contact SWS Sn (LP)



TE Part #1SNA163403R2000
CPP263

Documents

Product Drawings

6,35 FASTIN-FASTON RECEP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_160860-3_M.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_160860-3_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160860-3_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Product Specifications

[Application Specification](#)

English

[FASTIN-FASTON 110, 187, 205 And 312 Series Receptacle Contacts](#)

English

Agency Approvals

[UL Report](#)

English