

T1932241000-000 ✓ ACTIVE

HDC


TE Internal #: T1932241000-000

Heavy Duty Connector Base Housing, Bottom Entry, Screwlock,
Sealable

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Screwlock**

Sealable: **Yes**

EU RoHS Compliance: **Compliant**

Features

Operation/Application

Circuit Application

Power & Signal

Product Type Features

Hood & Base Connector Product Type

Base Housing

Sealable

Yes

Body Features

Cable Entry Location

Bottom

Mechanical Attachment

Hood & Base Locking Device Type

Screwlock

Other

EU RoHS Compliance

Compliant

EU ELV Compliance

Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1902244540-000
H24BPR-TG/SHC-M45/M40



TE Part # T1902242040-000
H24BPR-TG/SHC-M20/M40



TE Part # T1082241232-000
H24BPR-H130-TGHC-2M32



TE Part # T1902244020-000
H24BPR-TG/SHC-M40/M20



TE Part # T1902241229-000
H24BPR-TS/GHC-2PG29



TE Part # T1922241129-000
H24BPR-TGHC-PG29



TE Part # T1902241232-000
H24BPR-TS/GHC-2M32



TE Part # T1922241232-000
H24BPR-TGHC-M32/M25

TE Part # T1922241132-000
H24BPR-TGHC-M32TE Part # T1912241129-000
H24BPR-TSHC-PG29TE Part # T1912241121-000
H24BPR-TSHC-PG21TE Part # T1902242540-000
H24BPR-TG/SHC-M25/M40TE Part # T1912241140-000
H24BPR-TSHC-M40TE Part # T1082241240-000
H24BPR H130 -TG/SHC-2M40TE Part # T1922241221-000
H24BPR-TGHC-2PG21TE Part # T1990240010-000
H24BPRC-KDBPTE Part # T1912241125-000
H24BPR-TSHC-M25TE Part # T1922241121-000
H24BPR-TGHC-PG21TE Part # T1912241132-000
H24BPR-TSHC-M32TE Part # T1902243240-000
H24BPR-TG/SHC-M32/M40

Customers Also Bought

TE Part # T1922241140-000
H24BPR-TGHC-M40

Documents

Product Drawings

[H24BPR-AGC](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T1932241000-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1932241000-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1932241000-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Heavy Duty Connectors](#)

English

[HEAVY DUTY CONNECTORS](#)

English

[HEAVY DUTY CONNECTORS](#)

Japanese

Product Specifications

[Application Specification](#)

English

[Application Specification](#)