




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Gland**

Sealable: **Yes**

EU RoHS Compliance: **Compliant with Exemptions**

EU ELV Compliance: **Compliant with Exemptions**

Features

Product Type Features

Strain Relief Accessory Type	Cable Gland
Sealable	Yes

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (1.9% in Pb-Alloy in Copper) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.







Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T1610062216-000 H6B-SGRS-2PG16	 TE Part # T1912061116-000 H6BPR-TSHC-PG16	 TE Part # T1912062116-000 H6BPR-TSHC-PG16	 TE Part # T1620103416-000 H10B-SDRM-LB-PG16
 TE Part # T1200241616-000 H24B-TG/TS-PG16/2PG16	 TE Part # T1610103216-000 H10B-SGR-LB-2PG16	 TE Part # T1910102116-000 H10BPR-TSH-PG16	 TE Part # T1620061621-000 H6B-SDR-PG16/PG21
 TE Part # T1920060116-000 H6BPR-TGH-PG16	 TE Part # T1710102116-000 H10B-TBF-PG16	 TE Part # T1910061116-000 H6BPR-TSH-PG16	 TE Part # T1240241621-000 H24B-TGH-PG16/PG21



TE Part # T1240100216-000
H10B-TGH-2PG16



TE Part # T3161160050-000
LN-16-M, M16X1.5



TE Part # T1620103316-000
H10B-SDRM-LB-2PG16




TE Part # T1920100116-000
H10BPR-TGH-PG16



TE Part # T1220160216-000
H16B-TG-2PG16



TE Part # T1321060116-000
H6BN-TG-PG16




TE Part # T1910100116-000
H10BPR-TSH-PG16



TE Part # T1220240216-000
H24B-TG-2PG16

Customers Also Bought




TE Part #T2070244101-000
H24BN-T6-M




TE Part #T3609290101-000
DLX-29-MS



TE Part #2295044-4
RITS CONN. PLUG ASSY 4P YELLOW
TIN



TE Part #T1230240129-000
H24B-TSH-PG29



TE Part #T2070104101-000
H10BN-T3-M



TE Part #2312738-2
HMN-HD5-3-F



TE Part #2316315-2
HMN-HD1-24-M



TE Part #2316316-2
HMN-HD1-24-F



TE Part #2316663-2
HD1 TAB CONTACT AU0.38 M SIZE



TE Part #T2113000101-200
HMN-RJ45-M

Documents



Product Drawings

DLX-16-MS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T3609160101-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T3609160101-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T3609160101-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English