




AMP-LATCH

TE Internal #: 1658526-1
Wire-to-Board, 6 Position, 2.54 mm [.1 in] Centerline, 2 Row,
Receptacle, Wire & Cable, Signal, Cable Mount (Free-Hanging),
Ribbon Cable Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**
Number of Positions: **6**
Centerline (Pitch): **2.54 mm [.1 in]**
Row-to-Row Spacing: **2.54 mm [.1 in]**
Number of Rows: **2**

Features

Termination Features

Rectangular Termination Post & Tail Width	.46 mm[.018 in]
Rectangular Termination Post & Tail Thickness	.36 mm[.014 in]
Termination Method to Wire & Cable	Insulation Displacement (IDC)

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Thickness	2.54 – 5.08 µm[100 – 200 µin]
	30 µin
Wire Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	1 A

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
---------------------	---



Number of Rows	2
----------------	---

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability











Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these







limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 2-1761711-1 IDC LOW PRO HDR 6P VERT LG LAT</p>	 <p>TE Part # 2-1761608-1 IDC LOW PRO HDR 6P VERT SHT LA</p>	 <p>TE Part # 2-1761605-1 IDC LOW PRO HDR 6P RA BLUE</p>	 <p>TE Part # 2-1761607-1 IDC LOW PRO HDR 6P RA LG LAT B</p>
 <p>TE Part # 2-1761606-1 IDC LOW PRO HDR 6P VERT LG LAT</p>	 <p>TE Part # 1761681-1 IDC LOW PRO HDR 6P VERT HT BLACK</p>	 <p>TE Part # 2-1761603-1 IDC LOW PRO HDR 6P VERT BLUE</p>	 <p>TE Part # 2-1761713-1 IDC LOW PRO HDR 6P VERT SHT LA</p>
 <p>TE Part # 2-1437020-1 609-0631=FSKT IDC S 06 SR</p>	 <p>TE Part # 2-1761679-1 IDC LOW PRO HDR 6P VERT BLUE</p>		

Customers Also Bought

 <p>TE Part #223988-1 UNV PWR MDL, GUIDE PIN PLTD</p>	 <p>TE Part #5748271-1 FEMALE SCREWLOCK KIT</p>	 <p>TE Part #1625856-5 RH73 2A 30M 10% 100PPM 1K RL</p>	 <p>TE Part #1623448-1 CRG1206 1% 1K8</p>
--	--	--	--



TE Part #1393763-5
V23100V4005A11

TE Part #1-1676913-8
YR1 0.1% 1K62

TE Part #1-1438608-5
2POS MQS REC SEALED COD A

TE Part #621054-000
D-142-50

TE Part #1-1355524-3
MQS ABDECKKAPPE 12P

TE Part #1483351-3
MICRO-MATCH LEAD 06P 250MM

Documents

Product Drawings

609-0630LF FEM SOCKT,LEAD FREE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1658526-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1658526-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1658526-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English

Instruction Sheets

Instruction Sheet (U.S.)

English