

840-AG11D-ESL-LF

x OBSOLETE

DIPLOMATE

TE Internal #: 3-1571552-2

TE Internal Description: 840-AG11D-ESL-LF=800 DIP,GF/SN

DIP Socket: Standard, Stamped & Formed, Open, Gold

[View on TE.com >](#)



Connectors > Socket Connectors > IC Sockets > DIP Sockets > DIP Socket: Standard, Stamped & Formed, Open, Gold



Contact Fabrication: **Stamped & Formed**

Number of Positions: **40**

Connector Profile: **Standard**

Row-to-Row Spacing: **15.24 mm [.6 in]**

Contact Mating Area Plating Material: **Gold**

[All DIP Socket: Standard, Stamped & Formed, Open, Gold \(0\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Electrical Characteristics

Contact Resistance	10 mΩ
Insulation Resistance	5000 MΩ

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.18 mm[.125 in]

Housing Features

Housing Color	Black
Housing Material	Thermoplastic Polyester
Centerline (Pitch)	2.54 mm[.1 in]



Mechanical Attachment	
Connector Mounting Type	Board Mount
Mating Alignment Type	Polarization
Mating Alignment	With
Packaging Features	
Tubes per Box	100
Packaging Method	Tube, Box & Tube
Packaging Quantity	12
Operation/Application	
Circuit Application	Signal
Other	
Quantity per Tube	12
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant
Dimensions	
Product Length	50.8 mm[2 in]
Profile Height from PCB	2.67 mm[.105 in]
Row-to-Row Spacing	15.24 mm[.6 in]
Body Features	
Sleeve Plating Material	Tin
Frame Style	Open, Ladder
Sleeve Material	Brass
Connector Profile	Standard
Configuration Features	
PCB Mount Orientation	Vertical
Number of Rows	2
Number of Positions	40
Contact Features	
Mating Contact Type	Four-Fingered
Contact Base Material	Beryllium Copper
IC Socket Type	DIP



PCB Contact Termination Area Plating Material	Tin
Contact Type	Pin
Contact Fabrication	Stamped & Formed
Contact Mating Area Plating Material	Gold
	5 µin
Contact Current Rating (Max)	3 A

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #342103-1
22-16 F.E.P.G. RING TONGUE NO.



TE Part #2-1676480-5
CRG0402 1% 1K3




TE Part #1622326-1
LR1 1% 15R




TE Part #207608-6
SKT HDR ASSY,3 P,MMATE LF



TE Part #1623934-8
ZEROHM 0207 STEEL



TE Part #165616-2
110 PIDG FASTON REC



TE Part #CAT-D625-80007
DIP Socket: Standard, Stamped & Formed, Open, Gold



TE Part #2-1571552-4
816-AG11D-ESL-LF=800 DIP,GF/SN



TE Part #5227716-3
BNC SOLDER RECEPT JACK

Documents

Product Drawings

840-AG11D-ESL-LF=800 DIP,GF/SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1571552-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1571552-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1571552-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



DIP Sockets Quick Reference Guide (EN)

English