




Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)







EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>





Compatible Parts

 TE Part # 5536510-2 2MM FB,ASY,048,SIG,REC,SL,3.53	 TE Part # 5223650-2 2MM FB,4RV,REC,ASY,048,PF,4.25	 TE Part # 536510-2 2MM FB,ASY,048,SIG,REC,SL,3.53	 TE Part # 5536507-2 2MM FB,ASY,048,SIG,REC,SL,2.73
 TE Part # 5536511-2 2MM FB,ASY,048,SIG,REC,EN,3.55	 TE Part # 5223655-2 2MM FB,4RV,REC,ASY,048,SL,4.25	 TE Part # 5223660-2 2MM FB,4RV,REC,ASY,048,SL,3.20	

Also in the Series | Z-PACK Future Bus+

 Backplane Connector Housings(19)	 Board-to-Board Headers & Receptacles(14)	 Hard Metric Backplane Connectors(1)	 PCB Headers & Receptacles(14)
---	--	--	--

Customers Also Bought

 TE Part #CAT-AX41-IM11B Standard Signal Relay 2 Form C,2 CO Cont	 TE Part #1-1462038-6 IM06NS=IM RELAY 140mW 12V	 TE Part #1-2176230-1 3522 5R6 5% 3W	 TE Part #CAT-C339-SM1A SMD Power Resistor: 7 Watt, 0.10-500 Ohm
---	--	--	--



Documents

Product Drawings

2MM FB,ASY,048,SIG,HDR,EN,6.50

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_536504-2_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_536504-2_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_536504-2_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English