




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **20**

Number of Rows: **2**

Features

Operation/Application

Solder Process Feature	Board Standoff
------------------------	----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	7 mm[.276 in]

Body Features

Connector Profile	Standard
Primary Product Color	Black

Mechanical Attachment

PCB Mount Retention Type	Retention Solder Tails
PCB Mount Retention	With
Connector Mounting Type	Board Mount

Termination Features

--	--



Rectangular Termination Post & Tail Width	.69 mm[.027 in]
Rectangular Termination Post & Tail Thickness	.2 mm[.008 in]
Termination Post & Tail Length	3.1 mm[.122 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Mating Pin Diameter	.63 mm[.024 in]
	30 µin
Mating Square Post Dimension	.63 mm[.024 in]
PCB Contact Termination Area Plating Material Thickness	2.5 µm[98.425 µin]
Contact Shape & Form	Square
Contact Protection Type	Closed Entry Housing
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Socket
Contact Current Rating (Max)	3 A

Housing Features

Mating Entry Location	Top
Housing Material	Polyester - GF
Centerline (Pitch)	2.54 mm[.1 in]

Configuration Features

Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	20
Number of Rows	2

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Usage Conditions

--	--



Operating Temperature Range	-65 – 125 °C[-67 – 221 °F][-85 – 257 °F]
-----------------------------	--

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-147279-5  
20 MODII HDR DR SFMT B/A T&R LF



TE Part # 2-826634-0  
MOD2 PIN HEADER 20P



TE Part # 2-826664-0  
20P MOD2 STIFT LEI



TE Part # 2-826658-0  
20P AMPMODU II STIFT LEI




TE Part # 2-826656-0  
20P AMPMODU II STIFT LEI



TE Part # 2-826632-0  
20P AMPMODU II PIN HDR.

Also in the Series | AMPMODU HV-100/HV-190



Board-to-Board Headers & Receptacles(321)



PCB Headers & Receptacles(321)

Customers Also Bought



TE Part #1558660-7  
T9GV5L14-24



TE Part #280520-2  
12P AMPMODU II SHRD HDR, ST, 0.38 AU



TE Part #280514  
AMPMODU II REC. HSG, SINGLE ROW, 12 POS.




TE Part #6-2176091-4  
RP 2A 0.25W 267R 0.1% 25PPM 1K RL



TE Part #2321342-6  
TAB0.5X0.4,NANO MS, NANOMULTISPRING INDIU




TE Part #1337815-2  
50 OHM COAX SMB STR PLUG STR P



TE Part #3-215297-6  
36P HV100 REC CON. TE, 7.0MM



TE Part #1-2176250-0  
TJT 500W 33R 5%



Documents

Product Drawings

2X20P HV100 REC CON. TE, 7.0MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-215307-0\_F.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-215307-0\_F.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-215307-0\_F.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English