

HDP24-24-18PE-L015

✓ ACTIVE

DEUTSCH | DEUTSCH HDP, DEUTSCH HD

TE Internal #: HDP24-24-18PE-L015

18 Position Housing, Housing for Male Terminals, Wire-to-Panel,
Sealable, Black, Wire & Cable, Power, Panel Mount, -55 – 125 °C
[-67 – 257 °F], Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings



Number of Positions: 18

Connector & Housing Type: Housing for Male Terminals

Mating Pin Diameter: 1.6 mm, 2.4 mm, 3.6 mm [.063 in, .142 in, .094 in]

Connector System: Wire-to-Panel

Sealable: Yes

[All DEUTSCH HDP20 Housings \(357\)](#)

Features

Housing Features

Housing Material	PA 66 GF
------------------	----------

Industry Standards

IP Rating	IP67
UL Flammability Rating	UL 94V-0

Dimensions

Compatible Insulation Diameter Range	1.4 – 3.8 mm, 3.6 – 5.2 mm[.055 – .15 in][.14 – .204 in]
Product Width	47.6 mm[1.87 in]
Product Length	50.8 mm[2 in]
Connector Height	58.7 mm[2.31 in]

Packaging Features

Packaging Quantity	30
Packaging Method	Tray

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No



Mating Alignment Type	Polarizing Slot
Mating Alignment	With
Connector Mounting Type	Panel Mount

Other

Serviceable	Yes
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Electrical Characteristics

Operating Voltage	250 VDC
Nominal Voltage Architecture	250 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 8, Size 16, Size 12
Contact Type	Pin
Mating Pin Diameter	1.6 mm, 2.4 mm, 3.6 mm[.063 in][.142 in][.094 in]
Contact Current Rating (Max)	25 A, 13 A, 60 A

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Circular
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Panel
Sealable	Yes
Primary Locking Feature	Contact Retainer
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	0
Connector Modification	Threaded Adapter
Connector Seal Code	E Seal



Number of Positions

18

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # CAT-D48-ST273 DEUTSCH Solid Contacts	 TE Part # SRN21 SEAL RING, CONDUIT ADAPTER, NW22	 TE Part # HD30-24BT BOOT, 24SZ, ST, GRY	 TE Part # HD30-24BT-90-BK BOOT, 24SZ, RA, BLK
 TE Part # 114008-ZZ EXT TOOL, SIZE 8, 8-10 AWG, N, GRN	 TE Part # CAT-J67-DSCC16 DEUTSCH Size 16 Crimp Contacts	 TE Part # 1060-12-0166 PIN, SF, SIZE 12, 12-14, NI/SN	 TE Part # CAT-D48-SFT273 DEUTSCH Stamped and Formed Contacts
 TE Part # 62036-40 62036 HDP24 FLANGE-SEAL silicone 60shore	 TE Part # 0411-337-1205 EXT TOOL, SIZE 12, 12-14 AWG, E, ORG	 TE Part # 0411-336-1605 EXT TOOL, SIZE 16, 16-20 AWG, E, DRK BLU	 TE Part # CAT-H396-B128 DEUTSCH HDP20 Backshells
 TE Part # CAT-D48-SP729 DEUTSCH Sealing Plugs	 TE Part # 1060-12-0144 PIN, SF, SIZE 12, 12-14, AU/SN	 TE Part # 2300908-1 0460-003-16329, PIN, SOLID, 20- 24AWG, AU	 TE Part # CAT-H396-CH8172 DEUTSCH HDP20 Housings
 TE Part # 1060-12-0222 PIN, SF, SIZE 12, 10, NI/NI	 TE Part # HD30-24BT-BK BOOT, 24SZ, ST, BLK	 TE Part # 24-D-PUNCH D-HOLE PUNCH, SIZE 24	 TE Part # CAT-H396-RC8382 Receptacle Protective Caps — DEUTSCH HDP20

Also in the Series | **DEUTSCH HD**

HDP24-24-18PE-L015

18 Position Housing, Housing for Male Terminals, Wire-to-Panel, Sealable, Black, Wire & Cable, Power, Panel Mount, -55 – 125 °C [-67 – 257 °F], Hybrid




Automotive Connector Caps & Covers (4)



Automotive Housings(357)



Connector Strain Relief(5)



Other Automotive Connector Accessories(6)

Also in the Series | **DEUTSCH HDP**



Automotive Connector Caps & Covers (4)



Automotive Housings(357)




Connector Backshells(10)



Connector Seals & Cavity Plugs(1)



Insertion & Extraction Tools(11)



Other Automotive Connector Accessories(6)

Customers Also Bought



TE Part #CAT-AM7801-CH8172
AMPSEAL 16 Housings



TE Part #DT04-12PA-CE08
REC, 12P, GRY, E, ENH KEY, A



TE Part #HDP26-24-18PE-L017
PLG, 18P, BLK, E, RNG, 8/12/16, P




TE Part #3-640600-2
02P MTA156 CONN ASSY 20AWG LF



TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #1-1924067-4
2POS, MCON 1.2 CB REC 2p TL
SEALED



TE Part #282520-000
44A0311-18-0-US



Documents

Product Drawings

REC, 18P, BLK, E, THD, 8/12/16, P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HDP24-24-18PE-L015_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_HDP24-24-18PE-L015_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_HDP24-24-18PE-L015_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

DEUTSCH HD30 & HDP20 CONNECTOR SERIES

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English