



TE Internal #: 1-1337431-0
BNC Connector, Plug, 75 ohm, Bayonet, 4 GHz, Cable-to-Cable, 1
Position, Wire & Cable, Cable Mount (Free-Hanging), -55 – 85 °C
[-67 – 185 °F], Crimp
[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors



RF Interface: **BNC**
RF Connector Style: **Plug**
RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**
Impedance: **75 Ω**
Compatible With RF Cable Type: **URM 111, RG 187A, RG 179B, TM3289**

Features

Packaging Features

Packaging Quantity	50
Packaging Method	Box

Other

Coupling Nut Base Material	Brass
Gasket Material	Silicone Rubber
Grade	Professional
Dielectric Material	PTFE
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Contact Features

Crimp Type	Hexagonal Crimping
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]

Product Type Features

RF Interface	BNC
--------------	-----



RF Connector Style	Plug
Compatible With RF Cable Type	URM 111, RG 187A, RG 179B, TM3289
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Dimensions

RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]
---	-------------------

Electrical Characteristics

Impedance	75 Ω
-----------	------

Mechanical Attachment

RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Cable Mount (Free-Hanging)
RF Contact Captivation Method	Mechanical
Detent	With

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Plating Material	Nickel

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
SVHC > Threshold:
Pb (3.15% in Component)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-1337446-1
BNC Pnl Skt 75Ohm Silver Pltd

TE Part # 1050859-1
2002 5016 00

TE Part # 1052552-1
2052 1352 02,SMA FM JACK RECPT

Customers Also Bought

TE Part #T4141L12041-000
M12,REAR MOUNT,FEMALE,L,3P+PE, SOLDER PCB

TE Part #1838275-2
M12 Fld Ser CONN. Male Pin Sld


TE Part #L9000205-01
Antenna WiFi6/6E FPC LH 45x7 100 UFL

TE Part #CONSMA012-R178
SMA Plug 50 Ohm Cable Crimp





TE Part #CSJ-SGFB-100-MHF4
SMA to MHF4 100mm 0.81 OD



TE Part #7-1879663-1
H8 576R 0.1% 15PPM



TE Part #1337772-4
50/OHM COAX BNC STR PLUG ELB P



TE Part #4-1825136-0
A101SHZQ04



TE Part #4-2381880-7
PBES16 28 NO LAMP 1NC 1NO



TE Part #1337775-1
75 OHM COAX BNC STR PLUG P99-E

Documents

Product Drawings

BNC Str Plg Hex 75Ohm Nickel Pltd RG179B

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1337431-0_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1337431-0_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1337431-0_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English