



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**

Element Type: **Metal Oxide Film**

Power Rating: **.5 W**

Resistance Class: **Up to 1kΩ**

Resistance Value: **330 Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±350 ppm/°C

Electrical Characteristics

Operating Voltage	250 V
Power Rating	.5 W
Resistance Class	Up to 1kΩ
Resistance Value	330 Ω
Passive Component Tolerance	5 %

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Metal Oxide Film

Configuration Features

Number of Resistors	1
---------------------	---



Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	7.2 x 2.5 mm
------------------------------	--------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts




TE Part # 4-1625886-1
1W SM M/OX 5% 820K




TE Part # 1625881-2
1W STD M/OX 2% 220R



TE Part # 2-1625892-1
3W SM M/OX 5% 1K0



TE Part # 6-1676123-7
1/2W SM M/OX 5% 470R




TE Part # 1625893-5
5W SM M/OX 5% 47K

Also in the Series | [Neohm ROX](#)




[Through-Hole Resistors\(783\)](#)


Customers Also Bought




TE Part #4525DO-DS3BK001DPL
PRESS XDCR,DIGITAL,PSI RANGE



TE Part #966067-6
FER,WIRE,PL SLV,.75/18,L10,GREY,LP



TE Part #2319847-2
END STACK DIP 2P G RAISED TUBE



TE Part #7-1676123-5
1/2W SM M/OX 5% 1K0






TE Part #2176411-8

1/2W SM M/OX 5% 22K



TE Part #6-1676123-7

1/2W SM M/OX 5% 470R



TE Part #5-487508-5

TRIOMATE ASY H 6P L=3.175,LDFR



TE Part #6437288-4

SUPER SEAL 26POS CAP ASSY H AU



TE Part #2383938-2

TERMI-BLOK SMD MOUNT 180_2P_5 MM



TE Part #2383938-4

TERMI-BLOK SMD MOUNT 180_4P_5 MM

Documents

Product Drawings

1/2W SM M/OX 5% 330R

English

Datasheets & Catalog Pages

Flame Proof Power Metal Oxide Film Resistors - Type ROX Series - Tyco Electronics Passives

English