

2-323011-2

✓ ACTIVE

PIDG


TE Internal #: 2-323011-2

Slotted Ring Tongue Terminal, 26 – 22 AWG, #6 / M3.5 Stud, 3.68 mm [.145 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

[View on TE.com >](#)



Terminals & Splices > Ring Terminals > PIDG Slotted Ring Tongue Terminals



Ring Terminal Product Type: **Slotted Ring Tongue Terminal**

Wire Size: **202 – 810 CMA**

Stud Size: **#6, M3.5**

[All PIDG Slotted Ring Tongue Terminals \(6\)](#)

## Features

### Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

### Electrical Characteristics

Voltage Rating	300 V
----------------	-------

### Industry Standards

Government Qualified Terminal	No
-------------------------------	----

### Body Features

Product Weight	.294 g
----------------	--------

Insulation Sleeve Color	Yellow
-------------------------	--------

Stripe Color	Yellow
--------------	--------

### Packaging Features

Packaging Quantity	1000
--------------------	------

Packaging Method	Tape Mounted
------------------	--------------

### Product Type Features

Terminal Features	Slotted
Ring Terminal Product Type	Slotted Ring Tongue Terminal
Stud Size	#6, M3.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

#### Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

#### Dimensions

Wire Size	202 – 810 CMA
Stud Diameter	3.68 mm [.145 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	18.26 mm [.719 in]
Compatible Insulation Diameter (Max)	2.08 mm [.082 in]
Compatible Insulation Diameter Range	1.27 – 2.08 mm [.05 – .082 in]

#### Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

#### Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

#### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

#### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE  
2024 (241)  
Does not contain REACH SVHC

#### Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

#### Solder Process Capability

Not applicable for solder process capability





#### Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts




## Also in the Series | PIDG






Ring Terminals(588)



Spade Terminals(228)





Special Purpose Terminals(1)



Splices(41)

## Customers Also Bought

TE Part #CAT-3983178-PHBXVD  
CT 2mm Post Header Asmby: Box V DIPTE Part #CAT-AM7017-H8172  
AMP COMMON TERMINATION HOUSINGSTE Part #NB-PTCO-002  
Pt100, 2.0x2.3, Class B, PTFC101B1G0TE Part #216418-001  
22759/32-30-2TE Part #844453-001  
22759/32-30-0TE Part #GA250K9A4I  
DISC-DISCRETETE Part #9-1617814-0  
PS10-1Y = 25A HP SSR

## Documents

### Product Drawings

[TERMINAL,PIDG R SLTD 26-22 6](#)

English

### CAD Files

[3D PDF](#)

English

[Customer View Model](#)

[ENG\\_CVM\\_2-323011-2\\_R.3d\\_igs.zip](#)

English

[Customer View Model](#)

[ENG\\_CVM\\_2-323011-2\\_R.3d\\_stp.zip](#)

English

[Customer View Model](#)

[ENG\\_CVM\\_2-323011-2\\_R.2d\\_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Agency Approvals**

[CSA Certificate](#)

English