



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **12**
Number of Rows: **2**
Centerline (Pitch): **7.62 mm [.3 in]**

Features

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Mechanical Attachment

Mating Retention	Without
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Termination Features

Termination Post & Tail Diameter	2.39 mm, 1.01 mm[.04 in][.094 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Mating Pin Diameter	2.39 mm[.094 in]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material	Gold
Contact Type	Socket, Pin



Contact Current Rating (Max)	35 A
------------------------------	------

Housing Features

Housing Material	Thermoplastic Glass Reinforced
Centerline (Pitch)	7.62 mm[.3 in]

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	12
Number of Rows	2

Product Type Features

Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Black
-----------------------	-------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.5% in Component part) <small>Article Safe Usage Statements:</small>




Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #1473005-4
SEMI-HARD TRAY DDR2 SODIMM
SOCKET 200P 5




TE Part #5207908-4
STRAIN REL W/SCREW RET KIT




TE Part #1393219-3
PE014005




TE Part #5406721-1
MJ,RJ45,SMT,GRAY,22" REEL




TE Part #1-1419130-2
TSC-105L3H,000



TE Part #2336396-2
ASSEMBLY, LIGHT CONTROLLER
BASE, W/VENT



TE Part #CAT-J04-APHH
AMPSEAL PCB Right-Angle Headers



TE Part #CAT-AM78-H342
AMPSEAL PCB Vertical Headers

Documents

Product Drawings
CONN,PIN,CUSTOM CONN

English

CAD Files
Customer View Model
ENG_CVM_CVM_6643735-1_A.2d_dxf.zip

English



3D PDF

3D

Customer View Model

ENG_CVM_CVM_6643735-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6643735-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English