




TE Internal #: 1-5050871-0
Socket Length 7.32 mm [.288 in], PCB Hole Diameter 2.56 mm [.101 in], Open Bottom, 1.04 – 1.65 mm² Wire, 17 – 15 AWG, Cable-to-Board, Pin Sockets
[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets > Miniature Spring Sockets: Open Bottom, Beryllium Copper, 7.5A



Socket Length: 7.32 mm [.288 in]
PCB Hole Diameter: 2.56 mm [.101 in]
Socket Sleeve Style: Open Bottom
Wire Size: 17 – 15 AWG

[All Miniature Spring Sockets: Open Bottom, Beryllium Copper, 7.5A \(9\)](#)

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Method to Wire & Cable	Solder
Insertion Method	Hand/Semi-Automatic

Body Features

Sleeve Plating Material	Tin
Sleeve Material	Copper

Packaging Features

Packaging Method	Loose Piece, Bag
Packaging Quantity	2000

Other

Spring Material	Beryllium Copper
-----------------	------------------



EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Operation/Application

Solder Process Feature	None
Circuit Application	Power & Signal

Contact Features

Contact Spring Plating Material	Gold
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material Thickness	30 µm[30 µin]
Contact Spring Plating Thickness	.762 µm[30 µin]
Contact Current Rating (Max)	7.5 A

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Socket Sleeve Style	Open Bottom
Connector System	Cable-to-Board
Sealable	No

Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm[.031 – .125 in]
Socket Length	7.32 mm[.288 in]
PCB Hole Diameter	2.56 mm[.101 in]
Wire Size	17 – 15 AWG
Mating Pin Diameter Range	1.27 – 1.45 mm[.05 – .057 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)



Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Pin-in-Paste capable to 260°C
---------------------------	-------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-5050871-9
SOCKET,MIN-SPR W/H SN-AU SER-5

Customers Also Bought



TE Part #1879378-3
TLR 2512 3.0W R0005 1% 50PPM 2K RL



TE Part #280372-1
6P AMPMODU II SHRD HDR, ST, TIN



TE Part #5-146257-3
06 MODII HDR DRST B/A .100CL LF



TE Part #9-1879215-2
CPF 0402 41K2 0.1% 25PPM 1K RL





TE Part #1-2364570-4

[AVH19 FLT SS LK RNG GRN 12V16A](#)



TE Part #1622243-2

[LR0204 1% 47R](#)



TE Part #1-2176313-7

[RP 1E 0.1W 196K 0.1% 25PPM 1K RL](#)



TE Part #4-5332070-4

[SOCKET,MIN-SPR W/N SN-AU SER-4](#)



TE Part #C906593001

[FLHTC0311-0.25-0](#)



TE Part #1-1734839-0

[FPC CONN. 0.5MM PITCH T/C,10P](#)

Documents

Product Drawings

[SOCKET,MIN-SPR W/H SN-AU SER-5](#)

English

CAD Files

Customer View Model

[ENG_CVM_1-5050871-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-5050871-0_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-5050871-0_A.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.