




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.03 – 2.62 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

	.046 in
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Dimensions

Product Length	19.2 mm[.755 in]
Compatible Insulation Diameter Range	2.11 – 3.1 mm[.083 – .122 in]



Terminal Material Thickness	.41 mm[.016 in]
Wire Size	1.03 – 2.62 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Phosphor Bronze
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 281197-6 FF 187 REC 1.0-2.5MM2 PTBR	 TE Part # 2150157-2 OCEAN_2.0_Applicator-E-110F140OV-REA	 TE Part # 151667-4 FF 375 REC TERMINAL 11-10 AWG PBR	 TE Part # 2150157-1 OCEAN_2.0_Applicator-E-110F140OV-REM
 TE Part # 281197-5 FF 187 REC 1.0-2.5MM2 PTBR (RE REELING)	 TE Part # 7-2150157-7 OCEAN_2.0_SPARE_PART_KIT-110F140OV	 TE Part # 1-1579007-4 EXTRACTION TOOL	 TE Part # 4-1579007-3 EXTRACTION TOOL KIT

Also in the Series | FASTIN-FASTON 250

 Crimp Terminal Housings(207)	 Insertion & Extraction Tools(2)	 PCB Terminals(2)	 Quick Disconnects(250)
----------------------------------	-------------------------------------	----------------------	----------------------------

Customers Also Bought



TE Part #CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING



TE Part #174656-7
10 POS DL PLATE FOR PLUG MKII+



TE Part #335104-E
SRCBUG A 2,54 2 2 CSI 112 * K-AD
B500 J




TE Part #2406467-1
4POS,5.8X0.8,TAB HSG ASSY,180DEG,
UNSLD




TE Part #2383365-1
V23136A0103X153-SZ-CBOX




TE Part #544720-E
SRCBUG A 2,54 2 2 CSI 163 * K-AD
B500 J



TE Part #2435022-1
SWS,MCON 1.2,CVTY DIA,3.5-3.7,GRN



TE Part #2434996-1
AMP SUPERSEAL 1.5 SERIES 2P CA,
CONN KIT



TE Part #2435001-1
AMP SUPERSEAL 1.5 SERIES 4P CA,
CONN KIT

Documents

Product Drawings
FF 250 REC 1-2.5MM2 PB

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_160917-3_P.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_160917-3_P.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_160917-3_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

Application Specification

German