

SF-7ES1N8A8LB2S - Cable connector

1618209

<https://www.phoenixcontact.com/us/products/1618209>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, SPEEDCON, M23, number of positions: 4+3+PE, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 12 mm ... 15 mm, number of positions: 8, connection method: Crimp connection, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243175

Your advantages

- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly
- Flexible use: reliably connect cable diameters of 7.5 mm ... 18 mm
- Molded designs with preassembled cables on one or both sides

Commercial data

Item number	1618209
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB32
Product key	ABRBFB
Catalog page	Page 154 (C-2-2019)
GTIN	4046356584487
Weight per piece (including packing)	135.2 g
Weight per piece (excluding packing)	102.34 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Order information:	Order crimp contacts 4 x Ø 1 mm, 4 x Ø 2 mm separately
Safety note	
Safety note	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none">• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.• The products are suitable for applications in plant, controller, and electrical device engineering.• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.• Assembled products may not be manipulated or improperly opened.• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).• When using the product in direct connection with third-party manufacturers, the user is responsible.• For operating voltages > 50 V AC, conductive connector housings must be grounded• Ensure that the protective or functional ground has been properly connected.• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector• Only use tools recommended by Phoenix Contact• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.• Operate the connector only when it is fully plugged in and interlocked.• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.• Observe the minimum bending radius of the cable. Lay the cable without twisting it.• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting

SF-7ES1N8A8LB2S - Cable connector

1618209

<https://www.phoenixcontact.com/us/products/1618209>



warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Circular connector (cable-side)
Application	Power
Number of positions	8
Connection profile	4+3+PE
Shielded	yes
Coding	N
Thread type	M23

Material specifications

Seal material	FPM
Housing material	Metal

Connection data

Conductor connection	
Connection method	Crimp connection

Electrical properties

Contact	
Contact diameter	2 mm
Max. current	30 A
Nominal voltage U _N	630 V
Overshoot category	III
Degree of pollution	3
Rated surge voltage	6 kV

Contact	
Contact diameter	1 mm
Min. cross section	0 mm ²
Max. current	9 A
Nominal voltage U _N	250 V
Overshoot category	III
Degree of pollution	3
Rated surge voltage	4 kV

Connector

Connection 1	
Head design	Socket

Cable/line

External cable diameter	12 mm ... 15 mm
-------------------------	-----------------

SF-7ES1N8A8LB2S - Cable connector

1618209

<https://www.phoenixcontact.com/us/products/1618209>



Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Altitude	3000 m
Permissible humidity (storage/transport)	50 % ... 65 %

SF-7ES1N8A8LB2S - Cable connector


1618209

<https://www.phoenixcontact.com/us/products/1618209>




Drawings

Diagram



I = current strength, T = ambient temperature

Dimensional drawing



Dimensional drawing


SF-7ES1N8A8LB2S - Cable connector

1618209

<https://www.phoenixcontact.com/us/products/1618209>



Schematic diagram



Connector pin assignment

SF-7ES1N8A8LB2S - Cable connector

1618209

<https://www.phoenixcontact.com/us/products/1618209>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1618209>

cUL Recognized	Approval ID: E153698-20041116		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG
	600 V	18 A	12 - 12

UL Recognized	Approval ID: E153698-20041116		
	Nominal voltage U_N	Nominal current I_N	Cross section AWG
	600 V	27 A	12 - 12

cULus Recognized

SF-7ES1N8A8LB2S - Cable connector

1618209

<https://www.phoenixcontact.com/us/products/1618209>



Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SF-7ES1N8A8LB2S - Cable connector

1618209

<https://www.phoenixcontact.com/us/products/1618209>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9d4ad310-0c5a-45ce-b22a-f61bb92355d9

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com