

# CA-1RS1N8A6L00 - Device connector front mounting



1623629

<https://www.phoenixcontact.com/us/products/1623629>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 16+2+FE, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, Axial seal, Central fastening M20 x 1.5, can be positioned via a locking nut, coding: N

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial data

|                                      |                    |
|--------------------------------------|--------------------|
| Item number                          | 1623629            |
| Packing unit                         | 1 pc               |
| Minimum order quantity               | 1 pc               |
| Sales key                            | AB31               |
| Product key                          | ABRAEL             |
| Catalog page                         | Page 99 (C-2-2019) |
| GTIN                                 | 4055626191409      |
| Weight per piece (including packing) | 32.4 g             |
| Weight per piece (excluding packing) | 32.4 g             |
| Customs tariff number                | 85366990           |
| Country of origin                    | DE                 |

## Technical data

### Notes

Order information:

Order crimp contacts 16 x Ø 1 mm, 3 x Ø 1.5 mm separately

### Product properties

Product type

Circular connectors (device side)

### Connector

#### Insulating body

|   |  |
|---|--|
| Note  | Order information: Order crimp contacts 16 x Ø 1 mm, 3 x Ø 1.5 mm separately |
| Coding  | N  |
| Insulation body material                            | PA 6.6   |
| Insertion/withdrawal cycles                         | 100  |
| Connection method                                   | Crimp connection   |
| Contact switching type                              | Socket   |
| Application   | Signal   |
| Number of positions                                 | 19   |
| Direction of rotation                               | Standard   |
| Connection profile                                  | 16+2+FE  |
| Contact diameter <b>Power contacts</b>              | 1.5 mm   |
| Litz wire cross-section <b>Power contacts</b> min.  | 0.08 mm <sup>2</sup>   |
| Litz wire cross-section <b>Power contacts</b> max.  | 1 mm <sup>2</sup>  |
| Rated current <b>Power contacts</b>                 | 10 A   |
| Note  | for max. connection cross section  |
| Rated voltage                                       | 48 V AC  |
|   | 74 V DC  |
| Rated surge voltage                                 | 1.5 kV   |
| Oversupply category                                 | II   |
| Degree of pollution                                 | 3  |
| Contact diameter <b>Signal contacts</b>             | 1 mm   |
| Litz wire cross-section <b>Signal contacts</b> min. | 0.08 mm <sup>2</sup>   |
| Litz wire cross-section <b>Signal contacts</b> max. | 1 mm <sup>2</sup>  |
| Nominal current per signal contact                  | 8 A  |
| Note  | for max. connection cross section  |
| Rated voltage Signal contact                        | 48 V AC  |
| Rated surge voltage                                 | 1.5 kV   |
| Oversupply category                                 | III  |
| Degree of pollution                                 | 3  |
| Installation height                                 | 2000 m   |

# CA-1RS1N8A6L00 - Device connector front mounting

1623629

<https://www.phoenixcontact.com/us/products/1623629>



## Housing

|                                   |  |
|-----------------------------------|--|
| Housing material                  | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Type of locking                   | for standard and SPEEDCON interlock                                  |
| Pg screw connection               | none   |
| Degree of protection (plugged in) | IP67   |
| Thread type                       | M23  |


## Environmental and real-life conditions

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

Drawings

Schematic diagram



Connector pin assignment


# CA-1RS1N8A6L00 - Device connector front mounting

1623629

<https://www.phoenixcontact.com/us/products/1623629>



Dimensional drawing



Installation dimensions

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1623629>

|  <b>cUL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| Power  | 48 V                  | 6 A                   | 18 - 18           | -                    |
| Signal   | 48 V                  | 5 A                   | 18 - 18           | -                    |

|  <b>UL Recognized</b><br>Approval ID: E335019-20141210 |                       |                       |                   |                      |
|---|-----------------------|-----------------------|-------------------|----------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| Power   | 48 V                  | 10 A                  | 18 - 18           | -                    |
| Signal  | 48 V                  | 8 A                   | 18 - 18           | -                    |

| <b>cULus Recognized</b> |
|-------------------------|
|-------------------------|

# CA-1RS1N8A6L00 - Device connector front mounting

1623629

<https://www.phoenixcontact.com/us/products/1623629>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CA-1RS1N8A6L00 - Device connector front mounting

1623629

<https://www.phoenixcontact.com/us/products/1623629>



## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|   |         |
|---|---------|
| Environment friendly use period (EFUP)  | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |         |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | bc3e95e1-2604-409b-80d1-81975cedac22 |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)