




EMI & EMC Solutions > EMI Filters > Power Line Filters > Single Phase Filters > Single Phase Filters, Corcom EMC Series



Current Rating: **6 A**

Input Termination Type: **Wire Lead**

Output Termination Type: **Wire Lead**

Leakage Current (Max) (120VAC, 60Hz): **.21 mA**

Leakage Current (Max) (250VAC, 50Hz): **.36 mA**

[All Single Phase Filters, Corcom EMC Series \(0\)](#)

Features

Mechanical Attachment

Panel Mount Feature Type	Flange
--------------------------	--------

Product Type Features

Filtering Requirements	Filtered
Ground Choke Option	No
Input Termination Type	Wire Lead
Output Termination Type	Wire Lead

Electrical Characteristics

Current Rating	6 A
Leakage Current (Max) (120VAC, 60Hz)	.21 mA
Leakage Current (Max) (250VAC, 50Hz)	.36 mA
Operating Voltage	250 VAC

Other

EU RoHS Compliance	Compliant
--------------------	-----------



EU ELV Compliance

Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series |


Customers Also Bought




TE Part #1376389-1
5MM POWER KEY 3P PLUG HSG NUT




TE Part #6609020-2
1EB3=F7099 S0



TE Part #480054-3
FF 250 REC HSG 1P NYLON NAT




TE Part #1586017-2
2P FH PLUG VAL-U-LOK V0



TE Part #480053-3
FF 250 TAB HSG 1P NYLON NAT



TE Part #2-6609037-1
10EMC6=F8149



TE Part #6565204-1
TC-ZIF REC ASSY 260P



TE Part #350981-2
RING 18-14 AWG PTPBR



TE Part #569741-002
000W280



TE Part #1674569-1
LEVER, TC ZIF CONNECTOR

Documents

Product Drawings

6EMC3=F8147

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-6609037-9_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-6609037-9_C.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-6609037-9_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_1-6609037-9_A.3d_igs.zip

English



Customer View Model

[ENG_CVM_1-6609037-9_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-6609037-9_A.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE EMC SERIES](#)

English

Corcom Combined Selector Charts

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English