

368811-1

✓ ACTIVE

Econoseal J - Mark II


TE Internal #: 368811-1

Single Wire Seal (SWS), NBR, Gray, 1.8 – 2.1 mm [.071 – .085 in]

Insulation Diameter, Econoseal J - Mark II

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Seals & Cavity Plugs

Connector Seal & Plug Type: **Single Wire Seal (SWS)**Primary Product Material: **NBR**Primary Product Color: **Gray**Compatible Insulation Diameter Range: **1.8 – 2.1 mm [.071 – .085 in]**EU RoHS Compliance: **Compliant****Features****Packaging Features**

Packaging Method	Bag
Packaging Quantity	1000

Product Type Features

Connector Seal & Plug Type	Single Wire Seal (SWS)
----------------------------	------------------------

Body Features

Primary Product Material	NBR
Primary Product Color	Gray

Dimensions

Compatible Insulation Diameter Range	1.8 – 2.1 mm [.071 – .085 in]
--------------------------------------	-------------------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




Also in the Series | [Econoseal J - Mark II](#)




Automotive Connector Locks & Position Assurance(2)



Automotive Housings(16)



Connector Seals & Cavity Plugs(5)



Other Automotive Connector Accessories(3)

Customers Also Bought

TE Part #171631-1
E-J MK-2 070 TAB CONTTE Part #CAT-LMPH9507
Low & Medium Power HeaderTE Part #1-2406058-1
2POS,TAB2.8X0.8,HDR ASSY,180DEG,
COD ATE Part #2-1633620-0
ANVIL, COMBINATIONTE Part #2364846-1
2POS,DIA 8MM,SOC HSG ASSY,SLD,
COD ATE Part #344089-1
2W RECP. ANTI-BACKOUTTE Part #1633860-6
CRIMPER, WIRE FTE Part #2288928-1
BYD T75 6PIN/2PIN THROUGH WAL
CABLE ASSYTE Part #CT01843001
55E0119-0.75-7(B01)

Documents

Product Drawings

[.250 SEAL PLUG \(0.85-2.0 W SQ\)](#)

English

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_368811-1_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_368811-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_368811-1_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English