



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Rectangular Connector Insert Type: **Pneumatic Insert**

Sealable: **No**

EU RoHS Compliance: **Compliant**

Features

Product Type Features

Rectangular Connector Insert Type	Pneumatic Insert
Sealable	No

Other

EU RoHS Compliance	Compliant
--------------------	-----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T2090002101-001
PNEU-C-M1.6

Also in the Series

HDC HMN



Connector Contacts(2)




Connector Hardware(16)



Insertion & Extraction Tools(1)



Power Contacts(2)



Rectangular Contact Inserts(120)

Customers Also Bought





TE Part #ZPF000000000203708


[DMC-M 99-10 PC](#)

TE Part #ZPF000000000202098

[732-8052-18 WA](#)


TE Part #ZPF000000000201129

[732-8052-31 WA](#)



TE Part #ZPF000000000203398

[DMC-MR 30-23 PC](#)



TE Part #ZPF000000000203399

[DMC-MR 30-23 PD](#)



TE Part #CZ6862-000

[HEX40-AC-45-25-A12-3](#)



TE Part #225398-6

[CONNECTOR, BNC DUAL CRIMP JACK](#)



TE Part #ZPF000000000202094

[DMC-M 0402 AW 01](#)

Documents

Product Drawings

[PNEU-C-FW1.6](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_T2090012201-001_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2090012201-001_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2090012201-001_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HEAVY DUTY CONNECTORS](#)

English

[HEAVY DUTY CONNECTORS](#)

Japanese