




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**

Wire Size: **2050 – 5180 CMA**

Stud Size: **#10**

Features

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Insulation Sleeve Color	Blue
Stripe Color	Blue

Packaging Features

Packaging Quantity	5000
Packaging Method	Tape Mounted

Product Type Features

Stud Size	#10
Sealable	No
Wire Insulation Support Retention Type	Insulation Support



Contact Features

Spade Terminal Type	Spring Spade Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	4.82 mm [.19 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	23.37 mm [.92 in]
Compatible Insulation Diameter (Max)	4.9 mm [.193 in]
Compatible Insulation Diameter Range	3 – 4.9 mm [.118 – .193 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2392022-2 BLUE BATTERY DAHT KIT 220V (47387-7)	TE Part # 169400 CERTI-LOK FRAME W/O DIES	TE Part # 47387 DAHT PG PIDG 20-14 ASSY	TE Part # 59250 T-HEAD PIDG 26-14 ASSY
TE Part # 47807-1 DIES PIDG 16-14 DIE SET	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 58433-3 PRO CR ASSY, RBY IS9252	TE Part # 525691 DAHT PG PIDG 16-14 ASSY
TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	TE Part # 2392022-1 BLUE BATTERY DAHT KIT 110V (47387-7)	TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 169404 CERTI-LOK DIE



TE Part # 2063030-1
SDE DIESET, RBY, UL

TE Part # 47387-7
DAHT PG PIDG 16-12 ASSY

Also in the Series

PLASTI-GRIP

Compression Connectors(3)

Crimp Wire Pins, Tabs & Ferrules(20)

Ring Terminals(310)

Spade Terminals(159)

Splices(45)

Customers Also Bought

TE Part #1971783-1
PTL RECEPTACLE CONTACT, 16-19 AWG, 2X22

TE Part #58628-1
PROCRIMP T&D 26-14 ULTRAFAST

TE Part #2-34120-1
TERMINAL,SOLIS R 16-14 6


TE Part #52951-3
PG SPR SPD 22-16COM22-18MIL 10

TE Part #40523
RING TERMINAL 12-10 AWG TPBR

TE Part #52963
TERMINAL,PG SPR SPD 12-10 10

TE Part #3-1971776-3
PTL 2X3 PLUG HSG STD TEMP KEY C BLU

TE Part #58628-2
PROCRIMP DIESET 26-14 ULTRAFAST



Documents

Product Drawings

TERMINAL,PG SPR SPD 16-14 10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_53245-2_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_53245-2_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_53245-2_L.3d_stp.zip

English

Customer View Model

ENG_CVM_53245-2_L1.3d_igs.zip

English

Customer View Model

ENG_CVM_53245-2_L1.3d_stp.zip

English

Customer View Model

ENG_CVM_53245-2_L1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English

53245-2

Spring Spade Terminal, 16 AWG, #10 Stud, 4.82 mm [.19 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Partially Insulated, PLASTI-GRIP

