



Connectors > Automotive Connectors > Automotive Housings



Number of Positions: 2

Connector & Housing Type: Plug

Mating Tab Width: 2.3 mm [.09 in]

Centerline (Pitch): 5.6 mm [.22 in]

Sealable: Yes

Features

Product Type Features

Mixed & Hybrid Connector	No
Connector & Housing Type	Plug
Sealable	Yes
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	2
Number of Rows	1

Contact Features

Mating Tab Width	2.3 mm[.09 in]
------------------	----------------

Body Features

Primary Product Color	Ivory
-----------------------	-------

Housing Features

Centerline (Pitch)	5.6 mm[.22 in]
--------------------	----------------

Usage Conditions

--	--



Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Other

Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 936818-1
INNER SEAL(BULB PLUG 2P ASSY)

Customers Also Bought



TE Part #85205-1
JPT POWER TIMER 3P ASS'Y



TE Part #1-1813099-1
2.5mm SOCKET HSG ASSEMBLY
(BLACK 4 POS)



TE Part #1-968050-1
SPECIAL TERMINAL 11-10 AWG PTPB



TE Part #1813344-1
7p 1.5mm socket housing assy' coding
A



TE Part #1-2208709-1
91POS, MIXED, REC HSG, ASSY,
SEALED



TE Part #2301241-1
RETAINER, TAB HSG., 49POSN.,



TE Part #2358547-7
COVER, PROTECTIVE COVER



TE Part #3-2315660-2
2POS. RING TONGUE HSG, ASSY



TE Part #936204-1
090III 18P PLUG ASSY



TE Part #2322637-1
12POS, MQS, REC HSG, UNSLD

Documents

Product Drawings

BULB CONN 2P PLUG ASSY IVORY

English

CAD Files

Customer View Model

ENG_CVM_936184-1_A.3d_igs.zip

English

Customer View Model

936184-1

2 Position Housing, Plug, 5.6 mm [.22 in] Centerline, Sealable, Ivory, -30 – 105 °C [-22 – 221 °F]



[ENG_CVM_936184-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_936184-1_A.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.