

This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.



The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

ORIGINAL



REVISIONS			
SYM	ECN No.	DESCRIPTION	DATE By
A	NE-17052	RELEASE REVISION	04/24/2017 Arron Lin
B	NE-17271	ADD TAIL 3.30 OPTION	11/17/2017 Sondra Sang

NOTES:

- MATERIAL:
HOUSING: THERMOPLASTIC, PA9T, UL94V-0, COLOR: OPTIONS
COVER: THERMOPLASTIC, PA9T, UL94V-0, COLOR: OPTIONS
TERMINAL 5PIN: BRASS.
TERMINAL 4PIN: PHOSPHOR BRONZE,
SHELL: STEEL.
- FINISH:
TERMINAL:
CONTACT AREA: SELECTIVE GOLD PLATING ;
SOLDERING AREA: MATTE TIN PLATING 100 μ " THICKNESS MIN.;
UNDER PLATING: NICKEL PLATING 50 μ " THICKNESS MIN.OVERALL.
SHELL:
NICKEL PLATING 50 μ " THICKNESS MIN.OVERALL.
- PRODUCT SPECIFICATION REFER TO : PS-7425
- THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS PER DIRECTIVE 2011/65/EU FOR RoHS COMPLIANT.



RECESSED MOUNTING CONFIGURATION






P/N: GSB3111 X X X 5H4HR

CONTACT FINISH:
1: GOLD FLASH
2: 15u" GOLD
3: 30u" GOLD

DIM L /DIM S
5: 3.30 /3.30mm
9: 2.10 /2.10mm

INSULATOR & COLOR
4: BLACK
9: BLUE



RECOMMENDED PCB LAYOUT (TOP VIEW)

T=1.60±0.05MM;TOL:±0.05MM
KEEP OUT AREA

TOLERANCE	APPROVALS	DATE	TITLE		UNIT	SIZE	PART No.
X. ±0.30	DRAWN Sondra Sang	11/17/2017	USB 3.0 CONN. A TYPE RECEPTACLE R/A DIP TYPE W/FLANGE		mm	A3	GSB3111XXX5H4HR
X.X ±0.20	CHECKED Chenny Yeh	11/17/2017			SCALE	SHEET	DWG No.
X.XXX ±0.10	APPROVED Hank Hsu	11/17/2017			NA	1 OF 2	GSB3111XXX5H4HR
ANGULAR ±1°	DWG TYPE CUST DWG	PROJECT CODE OTHER					REV. B
UNLESS OTHERWISE SPECIFIED							

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.






The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.




ORIGINAL



REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	By
A	NE-17052	RELEASE REVISION	04/24/2017	Debby Huang
B	NE-17271	ADD TAIL 3.30 OPTION	11/17/2017	Sondra Sang



PACKAGING BY T&R	8.3	4.7	240	8	1920	GSB3111XXX5H4HR
	G/W KG	N/W KG	PCS/ REEL	REELS/ BOX	QUANTITY (PCS)	PART NUMBER

TOLERANCE		APPROVALS		DATE	TITLE		Amphenol®				
X. X.X ±0.30 X.XX ±0.20 X.XXX ±0.10		DRAWN Sondra Sang		11/17/2017	USB 3.0 CONN. A TYPE RECEPTACLE R/A DIP TYPE W/FLANGE		Amphenol Corporation				
		CHECKED Chenny Yeh		11/17/2017			Amphenol Taiwan Corporation				
ANGULAR ±1°		APPROVED Hank Hsu		11/17/2017			PART No. GSB3111XXX5H4HR				
UNLESS OTHERWISE SPECIFIED		DWG TYPE CUST DWG		PROJECT CODE OTHER			UNIT mm	SIZE A3	DWG No. GSB3111XXX5H4HR		REV. B
							SCALE NA	SHEET 2 OF 2			