


MULTI-BEAM

TE Internal #: 6450140-9
PCB Mount Receptacle, Vertical, Board-to-Board, 35 Position, 2.54 mm / 6.35 mm [.1 in / .25 in] Centerline, Fully Shrouded, Gold

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **35**
Number of Rows: **4**

Features

Electrical Characteristics

Operating Voltage	200 VDC, 60 VDC
-------------------	-----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Connector Width	11.94 mm[.47 in]
PCB Thickness (Recommended)	2.11 – 2.62 mm[.083 – .103 in]
Connector Height	12.7 mm[.5 in]
Connector Length	110.49 mm[4.35 in]

Packaging Features

Packaging Quantity	22
Packaging Method	Tray

Industry Standards

Glow Wire Rating	High Temperature Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Mechanical Attachment

Mating Retention	Without
------------------	---------

Mating Alignment Type	Guide Post
PCB Mount Retention Type	Hold-Down
PCB Mount Alignment Type	Hold-Down
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Length	3.43 mm[.135 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 2.54 µm[50 – 100 µin]
Contact Mating Area Plating Material Thickness	.076 µm[3 µin]
PCB Contact Termination Area Plating Material Thickness	2.54 – 5.08 µm[100 – 200 µin]
Contact Layout	Matrix
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Receptacle
Contact Current Rating (Max)	42 A

Housing Features

Housing Material	High Temperature Thermoplastic Glass-Filled
Centerline (Pitch)	6.35 mm, 2.54 mm[.25 in][.1 in]

Configuration Features

Number of Columns	17
Number of Loaded Positions	35
Number of Signal Positions	24
Number of Power Positions	11
PCB Mount Orientation	Vertical
Number of Positions	35
Number of Rows	4

Product Type Features

Mixed & Hybrid Header	Yes
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Black
-----------------------	-------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6450230-1


MBXL R/A HDR 5P+24S+1M+6P

Customers Also Bought



TE Part #3-643814-3

03P MTA100 CONN ASSY POL RIB



TE Part #174355-7

070 ECONOSEAL MARK-2 P/CAP 2P



TE Part #350561-3

UMNL PIN 24-18 .0126 PTPPHBZ



TE Part #174354-2

070 ECONOSEAL MARK-2 CAP 2P



TE Part #CQ50453001

RAY-101-6.0(10)



TE Part #5-6450832-9

MBXLE R/A HEADER

5P+2HDP+4P+64S




TE Part #1-1734346-1

STD USB TYPE B, R/A, SMT



TE Part #1643782-1

291-0170-00100B=TA CONN,PIN



TE Part #1-6450852-3

MBXL VER REC 22LP + 40S



TE Part #6643765-1

CONN,SKT,TOP DRAWER

Documents

Product Drawings

MBXL VERT RCPT 5P+24S+1M+6P



English

CAD Files

Customer View Model

ENG_CVM_CVM_6450140-9_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6450140-9_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6450140-9_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

Application Specification

English