




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **10**

Number of Rows: **1**

Features

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Dimensions

Connector Width	8.5 mm[.334 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	9.2 mm[.36 in]
Connector Length	39.54 mm[1.55 in]

Other

Position Locations Omitted	3, 5, 7, 9
Number of Blocked Positions	4
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features

Packaging Quantity	500
Packaging Method	Bag



Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Body Features

Connector Profile	Low
Primary Product Color	Natural

Mechanical Attachment

Mating Retention Type	Locking Tab
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Length	3.7 mm[.146 in]
Square Termination Post & Tail Dimension	1.14 mm[.045 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	.8 – 1.8 µm[31.5 – 70.86 µin]
Contact Size	1.14mm
Contact Mating Area Plating Material Thickness	1 µm[39.37 µin]
Contact Shape & Form	Square
PCB Contact Termination Area Plating Material Thickness	1 µm[39.37 µin]
Contact Layout	Inline
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin



Contact Type	Tab
Contact Current Rating (Max)	8 A

Housing Features

Housing Material	PBT
Centerline (Pitch)	3.96 mm[.156 in]

Configuration Features

Number of Loaded Positions	6
Number of Power Positions	10
PCB Mount Orientation	Vertical
Number of Positions	10
Number of Rows	1

Product Type Features

Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1123723-3 3.96 EP HDR ASSY 3P(NATURAL)	 TE Part # 1-1123723-6 3.96 EP HDR ASSY 6P(NATURAL)	 TE Part # 1-1744498-0 10P EP-II HOUSING, BLACK	 TE Part # 3-2316952-0 3.96 EP HDR ASSY 10P, NO PIN 7,9
 TE Part # 1-2316952-8 3.96 EP HDR ASSY 8P, NO PIN 2,5,7	 TE Part # 1-2316952-6 3.96 EP HDR ASSY 6P,NO PIN 2,4	 TE Part # 1-1123723-5 3.96 EP HDR ASSY 5P(NATURAL)	 TE Part # 1-2316952-0 3.96 EP HDR ASSY 10P, NO PIN 2,4,6,9
 TE Part # 1-1744416-0 10 POS EP II HSG, GLOW WIRE	 TE Part # 1-1123723-7 3.96 EP HDR ASSY 7P(NATURAL)	 TE Part # 1-1123723-0 3.96 EP HDR ASSY 10P(NATURAL)	 TE Part # 1-1318300-0 3.96 EP HDR ASSY 10P NAT/TUBE

Also in the Series | Economy Power



Connector Contacts(15)



Connector Hardware(2)



Power Contacts(9)



Rectangular Connector Housings(1)



Rectangular Power Connectors(57)




Wire-to-Board Connector Assemblies & Housings(141)



Wire-to-Board Headers & Receptacles (402)


Customers Also Bought



TE Part #1614770-4
BDS 2 A 250 10R 10%



TE Part #ZPF000000000136485
RECEPTACLE MALE FOR 12 PINS, CAL1,6



TE Part #EC9833-000
ZHD-SCE-3.2-50-S1-4



TE Part #1-1415543-5
RTE44110



TE Part #ASA158F12390235000
623 PLUG



TE Part #ZPF000000000205373
PLUG MALE ANG.90 CAL.20 - FXP



TE Part #YZ-KC-212751A-PY00
TOOL DISMOUNTING - FXP2



TE Part #55992-1
TERMINAL,AMPOWER R 2/0 5/16



TE Part #ZPF000000000205378
CONTACT MALE ANG.90, CAL20, 120MM2 - FXP



TE Part #ZPF000000000205388
CONTACT FEMALE CAL.20, M12 - FXP

Documents



Product Drawings

3.96 EP HDR ASSY 10P, NO PIN 3,5,7,9

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2316952-0_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2316952-0_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2316952-0_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English