

TE Internal #: L9000282-01

SMB Connector, Jack, 50 ohm, Snap-On, 0 – 6.5 GHz, 1 Position,
Printed Circuit Board, Board Mount, -65 – 165 °C [-85 – 329 °F],
Solder, Straight

[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors

RF Interface: **SMB**RF Connector Style: **Jack**Impedance: **50 Ω**RF Connector Coupling Mechanism: **Snap-On**Operating Frequency: **0 – 6.5 GHz**

Features

Packaging Features

Packaging Quantity	100
Packaging Method	Tray

Configuration Features

PCB Mount Orientation	Edge
Number of Positions	1
Number of Coaxial Contacts	1

Operation/Application

Circuit Application	Signal
Operating Frequency	0 – 6.5 GHz

Product Type Features

Connector Product Type	Connector Assembly
RF Interface	SMB
RF Connector Style	Jack
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Electrical Characteristics

Impedance	50 Ω
-----------	------

Mechanical Attachment

RF Connector Coupling Mechanism	Snap-On
Connector Mounting Type	Board Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Material Finish	Plated
Body Plating Material	Gold

Contact Features

RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Usage Conditions

Operating Temperature Range	-65 – 165 °C [-85 – 329 °F]
-----------------------------	-----------------------------

Other

Dielectric Material	PTFE
EU RoHS Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.34% in Component Part)
Halogen Content	Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
	Low Bromine/Chlorine - Br and Cl < 900

ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # CONSMB007-G
SMB Plug 50 Ohm Cable Crimp



TE Part # CONSMB012-G
SMB Plug 50 Ohm Cable Crimp

Customers Also Bought




TE Part #1-215079-4
MICRO-MATCH FOB.14P



TE Part #2-2176091-3
RP 2A 0.25W 97R6 0.1% 25PPM 1K RL



TE Part #2-2213772-7
AV22 SPL 3A MOVE RING LED RED 24V



TE Part #1-2176339-9
CRGCQ 0603 330R 1%



TE Part #4-2176391-6
RQ 1206 36K5 0.1% 10PPM 5K RL



TE Part #1-1879262-0
RP 2B 14K 0.1% 15PPM CUT LENGTH



TE Part #7-1879259-9
RP 2B 2K26 0.1% 15PPM CUT LENGTH



TE Part #6609008-4
10EJH1=F8047 S0



TE Part #474340-E
IDCTERM 1 I2426 1,10 KA 105 707
0007 J



TE Part #5-2176390-6
RQ 1206 4K32 0.1% 10PPM 5K RL

Documents

Product Drawings

SMB Jack .062 PCB Edge Mount

English

SMB Jack .062 PCB Edge Mount

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_L9000282-01_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_L9000282-01_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_L9000282-01_A.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMB Jack PCB Edge Mount Connector

English