

2-6450122-9  ACTIVE

#### MULTI-BEAM


TE Internal #: 2-6450122-9

PCB Mount Header, Right Angle, Board-to-Board, 30 Position, 2.54 mm / 6.35 mm [.1 in / .25 in] Centerline, Fully Shrouded, Gold, Through Hole - Solder

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Right Angle**

Connector System: **Board-to-Board**

Number of Positions: **30**

Number of Rows: **4**

#### Features

#### Electrical Characteristics

Operating Voltage	200 VDC, 60 VDC
-------------------	-----------------

#### Dimensions

Row-to-Row Spacing	2.54 mm [.1 in]
Connector Width	23.62 mm [.93 in]
PCB Thickness (Recommended)	2.11 – 2.62 mm [.083 – .103 in]
Connector Height	14.58 mm [.574 in]
Connector Length	69.85 mm [2.75 in]

#### Other

Position Locations Omitted	P1, P6
Number of Blocked Positions	2
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

#### Packaging Features

Packaging Quantity	33
--------------------	----

Packaging Method

Tray

**Industry Standards**

Glow Wire Rating

High Temperature Part - Not Glow Wire

UL Flammability Rating

UL 94V-0

**Usage Conditions**

Operating Temperature (Max)

105 °C[221 °F]

Operating Temperature Range

-55 – 105 °C[-67 – 221 °F]

**Mechanical Attachment**

Mating Retention

Without

Mating Alignment Type

Polarization

PCB Mount Retention Type

Hold-Down

PCB Mount Alignment Type

Hold-Down

PCB Mount Retention

With

PCB Mount Alignment

With

Connector Mounting Type

Board Mount

Mating Alignment

With

**Termination Features**

Termination Post &amp; Tail Length

3.43 mm[.135 in]

Square Termination Post &amp; Tail Dimension

.64 mm[.025 in]

Termination Method to PCB

Through Hole - Solder

**Contact Features**

Contact Underplating Material

Nickel

Contact Underplating Material Thickness

1.27 µm[50 µin]

Contact Size

.64mm

Contact Mating Area Plating Material Thickness

.076 µm[3 µin]

Mating Square Post Dimension

.64 mm[.025 in]

PCB Contact Termination Area Plating Material Thickness

2.54 – 5.08 µm[100 – 200 µin]

Contact Shape &amp; Form

Square

Contact Layout

Matrix

Contact Base Material

Copper Alloy

PCB Contact Termination Area Plating Material

Tin

Contact Mating Area Plating Material

Gold

Contact Type	Blade, Tab
--------------	------------

Contact Current Rating (Max)	42 A
------------------------------	------

### Housing Features

Housing Material	High Temperature Thermoplastic Glass-Filled
Centerline (Pitch)	6.35 mm, 2.54 mm [.25 in] [.1 in]

### Configuration Features

Number of Columns	12
Number of Loaded Positions	28
Number of Signal Positions	24
Number of Power Positions	6
PCB Mount Orientation	Right Angle
Number of Positions	30
Number of Rows	4

### Product Type Features

Mixed & Hybrid Header	Yes
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### Body Features

Primary Product Color	Black
-----------------------	-------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JUNE 2024

(241)

Candidate List Declared Against: JUNE 2024 (241)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl &gt; 900 ppm.


Solder Process Capability

Not reviewed for solder process capability


## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought



TE Part #2198325-3  
zSFP+ STACKED 2X2 RECEPTACLE ASSEMBLY



TE Part #2198318-8  
zSFP+ STACKED 2X1 RECEPTACLE ASSEMBLY



TE Part #2170744-5  
CAGE ASSEMBLY, 1X4, QSFP28, SPRING



TE Part #5646884-1  
2MMHM TYPE A/B 125 POS INVERSE



TE Part #2-1445097-6  
MICRO MNL HDR ASSY S/ROW AU LF




TE Part #2170773-3  
CAGE ASSY, QSFP28 1X1, SPRING, LP



TE Part #2204420-9  
MULTI-BEAM HD VERTICAL REC. 15S+3P+3P+15



TE Part #1-2110122-1  
IMP100S,R,RA5P16C,LG,39



TE Part #2007853-2  
IMP100S,H,V5P10C,UG,LEW39,4.9



TE Part #2007902-3  
IMP100S,H,V6P16C,UG,DEW39,5.5

## Documents

### Product Drawings

#### MBXL R/A HDR 6P+24S

English

---

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-6450122-9\\_E7.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-6450122-9\\_E7.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-6450122-9\\_E7.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Product Specifications

#### Application Specification

English