



TE Internal #: 1377389-1
Plug, Board-to-Board, 48 Position, 5.08 mm [.2 in] Centerline,
Printed Circuit Board, 3 Row, Right Angle, 16 Column, Eurocard
Connectors
[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Plug**
Connector System: **Board-to-Board**
Termination Post & Tail Length: **2.9 mm [.114 in]**
Number of Positions: **48**
Centerline (Pitch): **5.08 mm [.2 in]**

Features

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Product Type Features

Connector & Housing Type	Plug
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Standard
DIN Level	I

Configuration Features

Number of Positions	48
Number of Rows	3
PCB Mount Orientation	Right Angle
Number of Columns	16
Rows Loaded	Z, B, D
Number of Signal Positions	48



Termination Features

Termination Post & Tail Length	2.9 mm[.114 in]
--------------------------------	-----------------

Housing Features

Centerline (Pitch)	5.08 mm[.2 in]
--------------------	----------------

Dimensions

Row-to-Row Spacing	3.81 mm[.15 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Not Compliant
EU ELV Compliance	Not Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides





on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 5148020-5 ASSY,PIN,EURO,"C/2",L-FREE,48</p>	 <p>TE Part # 650478-5 048 EURO TYPE C PIN ST ASSY</p>	 <p>TE Part # 5650948-5 ASSY,PIN,EUROCARD,TYPE C/2,LEA</p>	 <p>TE Part # 5535070-5 ASSY,RECEPTACLE,EUROCARD,TYPE</p>
 <p>TE Part # 5650916-5 ASSY,PIN,EUROCARD,TYPE C/2,LEA</p>	 <p>TE Part # 5536397-5 ASSY,RECEPT,EURO,TYPE C/2,LEAD</p>	 <p>TE Part # 5650479-5 ASSY,PIN,EUROCARD,TYPE R/2,LEAD-FREE,48</p>	

Customers Also Bought

 <p>TE Part #1241050-3 2x3P MOD II BREAK AWAY HDR,SMD,BLISTER</p>	 <p>TE Part #2-2823408-0 20P,2MM,PL HDR,DRVT,2.8,0.76AU,TB</p>	 <p>TE Part #1-2176186-7 CRGH1206 1% 2K7 0.5W</p>	 <p>TE Part #9-1879501-3 CRGH2512 5% 6K8 2W</p>
 <p>TE Part #2047723001 FLHTC0311-0.25-2</p>	 <p>TE Part #234451-E SRCP 1,27 3 F 1 I2426 137 * 162 1,07 TRA</p>	 <p>TE Part #2-2316110-0 20P,2MM,REC,HSG,DR,CRIMP,LATCH,BOX</p>	 <p>TE Part #354741-E STVF 48 F ZBD GGG 7-03 0606 4,5 * 207 E0</p>



Documents

Product Drawings

48P.IEC-F MALE CONN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1377389-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1377389-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1377389-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Workmanship Specification

English