




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **28**

Number of Rows: **4**

Features

Electrical Characteristics

Operating Voltage	200 VDC, 60 VDC
-------------------	-----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Connector Width	11.94 mm[.47 in]
PCB Thickness (Recommended)	2.11 – 2.62 mm[.083 – .103 in]
Connector Height	12.7 mm[.5 in]
Connector Length	59.69 mm[2.35 in]

Industry Standards

Glow Wire Rating	High Temperature Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Mechanical Attachment

Mating Retention	Without
PCB Mount Retention Type	Hold-Down
Mating Alignment Type	Guide Post
PCB Mount Alignment Type	Hold-Down

PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Length	3.43 mm[.135 in]
Termination Method to PCB	Through Hole - Press-Fit

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 2.54 µm[50 – 100 µin]
Contact Mating Area Plating Material Thickness	.076 µm[3 µin]
PCB Contact Termination Area Plating Material Thickness	2.54 – 5.08 µm[100 – 200 µin]
Contact Layout	Matrix
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Receptacle
Contact Current Rating (Max)	42 A

Housing Features

Housing Material	High Temperature Thermoplastic Glass-Filled
Centerline (Pitch)	6.35 mm, 2.54 mm[.25 in][.1 in]

Configuration Features

Number of Columns	10
Number of Loaded Positions	28
Mating & Unmating Configuration	Sequencing
Number of Signal Positions	24
Number of Power Positions	4
PCB Mount Orientation	Vertical
Number of Positions	28
Number of Rows	4

Product Type Features

Mixed & Hybrid Header	Yes
-----------------------	-----



Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Black
-----------------------	-------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU ELV Compliance	Compliant
-------------------	-----------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: DEC 2012 (138) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished



product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 1-6600333-6
MBXL VERT HDR 2P+24S+2P

Also in the Series | MULTI-BEAM XLE

Board-to-Board Headers & Receptacles(99)

PCB Headers & Receptacles(99)

Rectangular Power Connectors(12)

Customers Also Bought

TE Part #1614770-4
BDS 2 A 250 10R 10%

TE Part #ZPF000000000136485
RECEPTACLE MALE FOR 12 PINS, CAL1,6

TE Part #EC9833-000
ZHD-SCE-3.2-50-S1-4

TE Part #1-1415543-5
RTE44110

TE Part #ASA158F12390235000
623 PLUG

TE Part #ZPF000000000205373
PLUG MALE ANG.90 CAL.20 - FXP

TE Part #YZ-KC-212751A-PY00
TOOL DISMOUNTING - FXP2

TE Part #55992-1
TERMINAL,AMPOWER R 2/0 5/16



TE Part #ZPF00000000205378
CONTACT MALE ANG.90, CAL20,
120MM2 - FXP



TE Part #ZPF00000000205388
CONTACT FEMALE CAL.20, M12 - FXP

Documents

Product Drawings

VERTICAL RECP,2P+ 24S + 2P

English

CAD Files

Customer View Model

ENG_CVM_CVM_6-6450550-6_T3.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-6450550-6_T3.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-6450550-6_T3.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

Application Specification

English