

AMP Mini CT


TE Internal #: 2-292216-8

Connector Assembly, Plug to Plug Relay Header, Wire-to-Panel, 28
Position, 1.5 mm [.059 in] Centerline, 2 Row, Natural, Signal, AMP
Mini CT

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug to Plug Relay Header**

Connector System: **Wire-to-Panel**

Number of Positions: **28**

Centerline (Pitch): **1.5 mm [.059 in]**

Features

Electrical Characteristics

Operating Voltage	50 VDC
-------------------	--------

Industry Standards

Compatible With Agency/Standards Products	UL, CSA
UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL Recognized

Packaging Features

Packaging Method	Bag & Box
Packaging Quantity	200

Contact Features

Contact Layout	Matrix
Contact Retention Within Housing	Without
Contact Base Material	Brass
Contact Type	Pin
Contact Current Rating (Max)	2 A

Mechanical Attachment

Panel Mount Feature Type	Latches
Strain Relief	Without
Panel Mount Feature	With



Mating Retention Type	Locking Latch
Mating Retention	With
Connector Mounting Type	Panel Mount

Dimensions

Panel Thickness (Recommended)	.81 – 1.6 mm [.032 – .063 in]
Connector Height	11.2 mm [.44 in]
Connector Length	32.1 mm [1.264 in]
Row-to-Row Spacing	2 mm [.078 in]

Housing Features

Housing Material	Nylon 66
Centerline (Pitch)	1.5 mm [.059 in]

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug to Plug Relay Header
Connector System	Wire-to-Panel
Sealable	No

Configuration Features

Number of Positions	28
Number of Rows	2

Body Features

Primary Product Color	Natural
-----------------------	---------

Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Operation/Application


Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-353294-8
AMP MINI D/R HDR HSG 28P NATU



TE Part # 1-353293-4
MINI CT MT REC ASSY 14P GRAY




TE Part # 1-353908-4
CT REC HSG 14P CRIMP TYPE WHIT


Also in the Series | AMP Mini CT



Connector Contacts(4)




Connector Hardware(10)



PCB Headers & Receptacles(332)



Wire-to-Board Connector Assemblies & Housings(172)



Wire-to-Board Headers & Receptacles (332)

Customers Also Bought



TE Part #CAT-AM7017-H8172
AMP COMMON TERMINATION HOUSINGS



TE Part #5787169-7
68 50SR R/A RCPT ASSY,RDSN L/F



TE Part #1-353293-3
MINI CT MT REC ASSY 13P GRAY



TE Part #2-353294-4
AMP MINI D/R HDR HSG 24P NATU



TE Part #2-353294-6
AMP MINI D/R HDR HSG 26P NATU



TE Part #2-353294-8
AMP MINI D/R HDR HSG 28P NATU



TE Part #1-1879208-3
CPF 0402 33R 0.1% 25PPM 1K RL



TE Part #1-292254-3
CT RELAY HDR ASSY 13P NAT



TE Part #2-292215-4
MINI CT SGL RELAY 4P BLACK

Documents



Product Drawings

MINI CT D/R RELAY 28P V NAT

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_2-292216-8_O.3d_igs.zip

English

Customer View Model

ENG_CVM_2-292216-8_O.3d_stp.zip

English

Customer View Model

ENG_CVM_2-292216-8_O.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-292216-8_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-292216-8_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-292216-8_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Workmanship Specification

English