



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: .32 – .82 mm²

Mating Tab Width: 5.21 mm [.205 in]

Mating Tab Thickness: .81 mm [.032 in]

Features

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-2

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple



Other

Barrel Color	Red
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features

Packaging Quantity	2200
Packaging Method	Strip/Reel

Dimensions

Product Length	14.73 mm[.58 in]
Compatible Insulation Diameter Range	4.19 mm[.165 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm²

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	5.21 mm[.205 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Flag
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Closed

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150252-2
OCEAN_2.0_APPLICATOR-E-201D-SEA



TE Part # 7-2150252-7
OCEAN_2.0_SPARE_PART_KIT-201D



TE Part # 90390-3
DIES ULTRA-FAST FASTON 22-18 DIE SET

Also in the Series | ULTRA-FAST 205




Quick Disconnects(3)


Customers Also Bought



TE Part #2132781-6
06P EP-II HOUSING, NATURAL



TE Part #1217332-1
187 FASTON,PCB TAB,TCBR



TE Part #521781-1
250 HSG. PL MKIII REC. 6.81mm 4P NAT



TE Part #63475-2
187 FASTON REC 20-16 AWG TPBR



TE Part #928247-3
3P ST-TIMER GEH



TE Part #2371403-2
SGI 1.5 RCPT Contact, 24-28AWG



TE Part #2238136-2
RECEPTACLE, POSITIVE-LOCK, RAST 6.35



TE Part #2364484-1
250 FASTON HSG.,REC.,4 POS, NATRUAL



TE Part #2238212-2
RECEPTACLE, POSITIVE-LOCK, RAST 6.35



TE Part #2364485-1
250 FASTON HSG.,REC.,3 POS, NATRUAL

Documents

Product Drawings

205 ULTRA-FAST ASY REC FLAG 22-18 TPBR

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-521164-2_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-521164-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-521164-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Ultra-Fast and Ultra Fast Plus

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English