



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Keying Plug**

Primary Product Color: **Natural**

Primary Product Material: **PA 66**

Operating Temperature (Max): **105 °C [ 221 °F ]**

Operating Temperature Range: **-55 – 105 °C [ -67 – 221 °F ]**

Features

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-2 |
|------------------------|----------|

Packaging Features

|                    |         |
|--------------------|---------|
| Packaging Method   | Package |
| Packaging Quantity | 1       |

Product Type Features

|                                   |                 |
|-----------------------------------|-----------------|
| Connector Hardware Accessory Type | Keying Plug     |
| Hardware Accessory Function       | Coding & Keying |

Body Features

|                          |         |
|--------------------------|---------|
| Primary Product Color    | Natural |
| Primary Product Material | PA 66   |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature (Max) | 105 °C[221 °F]             |
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |

Other

|  |  |
|--|--|
|  |  |
|--|--|



|                    |           |
|--------------------|-----------|
| EU RoHS Compliance | Compliant |
| EU ELV Compliance  | Compliant |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts











TE Part # 213852-1  
CPC PLUG ASSEMBLY SIZE 23-19



TE Part # 211824-1  
CPC PLUG ASSEMBLY SIZE 23-13



TE Part # 207485-1  
CPC PLUG ASSEMBLY SIZE 23-16



TE Part # 213848-1  
CPC PLUG ASSEMBLY SIZE 23-37



TE Part # 211768-1  
CPC PLUG ASSEMBLY SIZE 17-9



TE Part # 213850-1  
CPC PLUG ASSEMBLY SIZE 23-37



TE Part # 796449-1  
PLUG ASSY,CPC,17-14,REV SEX



TE Part # 213851-1  
CPC PLUG ASSEMBLY SIZE 23-24



TE Part # 796450-1  
PLUG ASSY,CPC,17-9,REV SEX

Customers Also Bought




TE Part #1-6609021-2  
10VB6=F7353 S0



TE Part #3-643498-6  
06P MTA100 CONN ASSY LF



TE Part #206153-1  
11-4 F.H. RECEPT. STD. SEX



TE Part #747717-2  
LATCHING BLOCK KIT




TE Part #1-66358-8  
III+ SKT,18-14,TIN ,STRIP





TE Part #2-1625886-7  
1W SM M/OX 5% 5K1



TE Part #CAR3PC68  
CAR PLUG DIN9680 3way, IP68



TE Part #3-1614959-9  
CPF0805 1M91 0.1% 25PPM 1K RL



Documents

Product Drawings

CMNL KEYING PLUG

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_200821-1\_M.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_200821-1\_M.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_200821-1\_M.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M\_SERIES\_PIN\_AND\_SOCKET\_CONNECTORS

English

SOFT\_SHELL\_PIN\_SOCKET\_CONNECTORS\_STANDARD\_DENSITY

English

Instruction Sheets

Instruction Sheet (U.S.)

English