




Connectors > Terminal Blocks & Strips > Barrier Strips



Number of Positions: 2

Barrier Strip Style: Tri-Barrier

Bottom Termination Type: Printed Circuit Pin

Connector System: Wire-to-Board

Centerline (Pitch): 11.1 mm [.438 in]

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
Packaging Quantity	270

Operation/Application

Circuit Application	Power
---------------------	-------

Mechanical Attachment

Top Termination Type	Wire Clamp Combo Head
Mounting Options	None
Screw Plating Material	Zinc
Screw Material	Steel
Thread Size	8-32
Screw Head Type	Wire Clamp Combo Head
Connector Mounting Type	Board Mount



Contact Features	
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	30 A
Dimensions	
Product Length	24.07 mm[.948 in]
Wire Size	18 – 10 AWG, 22 – 10 AWG
Housing Features	
Housing Material	Thermoplastic
Centerline (Pitch)	11.1 mm[.438 in]
Product Type Features	
Block Style	Flat Bottom with standoffs
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board
Body Features	
Primary Product Color	Black
Product Orientation	Vertical
Barrier Strip Style	Tri-Barrier
Configuration Features	
Number of Levels	1
Number of Positions	2
Number of Rows	1
Termination Features	
Bottom Termination Type	Printed Circuit Pin
Electrical Characteristics	
Operating Voltage	600 V
Usage Conditions	
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
Other	
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Buchanan 8 Series



Barrier Strips(61)


Customers Also Bought




TE Part #6-103166-5
34 MODII HDR DRRA SHRD LF



TE Part #4-1625886-6
1W SM M/OX 5% 8R2



TE Part #2176346-9
CRGCQ 1210 22R 5%



TE Part #4-1617752-5
FCA-215-HZ4



TE Part #5-1614893-5
CPF 0805 49K9 0.1% 25PPM 1K RL




TE Part #4-2176609-2
EP 1W (SSS) 51R 5%




TE Part #1-2176609-9
EP 1W (SSS) 5R6 5%



TE Part #6-2176613-1
EP 4W (SS) 330R 5%



TE Part #10202301-00
PRESS XDCR M5244-000004-01KPG



TE Part #1589678-1
N11875 = HEADER

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_5-1437657-7_R1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_5-1437657-7_R1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1437657-7_R1.3d_igs.zip



English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.